

axial tool holder for lathes, DIN ISO 10889-4
square section adapter



Application:

For mounting lathe tools for internal and external machining.

Version:

- no. 227 15035-045 holder shape C1, right axial
- case-hardened HRC 58 +/- 2
- all functional surfaces sanded
- with ball nozzle

Art. no.	22715 035
VDI mount diameter	30 mm
Height	16/20 mm
Form	C1 R
Holder support length	70 mm
DIN	69880-1

