

Swarf containers, manual tipping

with low tipper edge height

Application:

For the collection and separation of liquids from solids and for the transport or disposal of all types of waste, bulk materials, chips and mass-produced parts.

Execution:

- Screen plate and drain valve 1" for separating liquids from solids
- Tilttable trough with handle
- Base frame with fork pockets
- Optionally box-shaped or low trough
- Safety chain to prevent slipping
- Protection against accidental tipping

Advantage:

- Due to the limited installation height, suitable for the case of low chip ejection
- Particularly suitable for collecting chips
- With floor-level emptying option

Delivery:

Goods supplied without packaging as standard. Packaging on request.



Art. no.	50266 433
Volume	0.8 m ³
Length	1420 mm
Width	910 mm
Tipper edge height	560 mm
Height	975 mm
Fork pocket clearance	525 mm
Fork pocket size (W x H)	170 x 55 mm
With drain valve	Yes
With stacker seat tilt function	No
With perforated sheet	Yes
Load-carrying capacity	300 kg
Surface	Lacquered
Colour	Light blue RAL 5012
Gross Weight	133.000 kg
Product Group	5AI

EAN

4052462040199