

## Carbide milling bits with INOX steel teeth (with teeth in accordance with DIN 8033)

Shank diameter 6 mm



### Application:

Deburring, machining contours, chamfering/rounding edges, milling out for preparation of deposit welds, preparation/levelling of welding seams, cleaning cast metal, changing geometries.



### Advantage:

- Extremely high cutting performance on all austenitic, rust and acid-resistant steels, stainless steel (INOX)
- Significantly reduced vibration and less noise

<b>Art. no.</b>	<b>76007 015</b>
<b>Brand</b>	PFERD
<b>Manufacturer Part Number</b>	4007220952245
<b>Form</b>	Cylindrical
<b>Head diameter x cutting edge length</b>	8 x 20 mm
<b>Cutting edge length</b>	20 mm
<b>Length</b>	60 mm
<b>Serration type</b>	INOX
<b>Gross Weight</b>	0.026 kg
<b>Product Group</b>	6AB

### EAN

4007220952245