

Allround Welding glove (TIG)

Designed for dexterity and best welding protection

Technical specification



Name	Allround Welding glove (TIG)	Art. No	SGTW01	
Glove purpose	EN388:3122, EN407 413X4X, EN12477/A1 Type A	Grip	Moderate dry grip	
Materials	Goat leather 0,8mm, Cow split leather 1,2mm, Para aramide sewing thread, cotton full lining.	Breathing	Good breathing	
Fitting (elastic tight, tight, close, loose)	The glove has a close fit, strongly rotated fingers improve fit	Disposal	No special waste	
PROTECTION LIMITS AND COMMENTS	Abrasion	Moderate abrasion resistance	Storage and cleaning notice	
	Cut	No cut resistant materials	No wash, store in cool, dry and dark place	
	Tear	Low to moderate tear resistance		
	Heat and insulation	Glove provide good insulation and good resistance to contact heat (100C) and in not flammable	Chemical safety	Reach compliance
	Water/ Oil	Goat leather has some water resistance	Colour	Yellow with white inner hand
	Puncture	Low (to moderate) puncture resistance(1,0mm flat tip) and needle (0,1mm flat tip) resistance and almost no hypodermic needle resistance (not cut or puncture proof)proof)	Sizes	7-11
Glove thickness	Palm 0,8mm plus lining	Packaging	6 pairs per bag/ 10 bags per case. 60 pairs per carton	
		Classification		

2013-02-12

Y. Berger & Co AB
 Ingela Gathenhielms gata 3
 SE 421 30 Västra Frölunda, Sweden
 +46 31 49 09 40
www.eurekasafety.se

