

Pneumatic turbine grinder TVD 365/2

80 watt



Application:

For working with milling pins of head diameter of up to 6 mm.

Execution:

- Air discharge to the rear
- Controlled rotational speed for constant speeds
- Run-out brake for increased safety
- With elastic bearing

Advantage:

- Constant speed at different loads thanks to centrifugal governor.
- Turbine motor - oil-free operation

Delivery:

Includes collet chuck ZG 5/3 mm, collet chuck key size 6 + 8 and hose unit; in box



Art. no.	75036 405
Brand	BIAX DRUCKLUFT
Manufacturer Part Number	150149730
Model	T 365/2
Valve design	Rotary valve
Motor design	Turbine motor
Max. idle speed	65000 rpm
Power output	80 W
Air consumption	180 l/min
Sound-pressure level	70 dB
Inner hose diameter	4 mm
Length	164 mm
Diameter of housing	17/38 mm
Max. clamping diameter	3 mm
Collet chuck diameter	3 mm
Suitable for max. sanding block diameter	8 mm
Max. HM rotating milling cutter diameter	6 mm
Weight	0.22 kg
Gross Weight	1.133 kg
Product Group	748