


SECUMAX MOBILEX NO. 45137.00

Adjustable cutting depth. You choose!

Paper, film, foam? Not a problem at all! But wait, there's more! The SECUMAX MOBILEX is the only safety knife with a concealed blade and an adjustable cutting depth. Make blade access larger or smaller by setting the in-built cutting depth adjuster. Set a depth ranging from low 2 mm to great 10 mm. It all depends on your requirements and the size of the material you need to cut.



Application




SECUMAX COUPPY NO. 43136.00

Make way for the specialist.

An expert in cutting flat paper and plastic sheets? You've found it in the handy SECUMAX COUPPY. Its concealed blade lies at a 45 degree angle to the cutting material. An optimal angle for easy cutting. A flat, clean base allows the safety knife to slide smoothly. The cleverly rounded head of the knife intuitively guides the cutting material towards the blade.



Application




PRODUCT FEATURES NO. 45137.00

Technical features



Main cutting materials



» all cutting materials from page 123 onwards

ACCESSORIES

	ORDER NO.
USED BLADE CONTAINER	NO. 9810.08
WALL MOUNT BRACKET USED BLADE CONTAINER	NO. 9845.06
SAFEBOX	NO. 108000.00

» further information from page 113 onwards

PRODUCT DETAILS

Knife size (L x W x H)	114 x 15.5 x 59 mm
Main material	Plastic
Weight	47.5 g
Weight per unit (self-service card)	58.4 g

ALL MODELS	ORDER NO.
SECUMAX MOBILEX with INDUSTRIAL BLADE NO. 37020 1 on self-service card (5 in multipack)	NO. 45137.00

MOUNTABLE BLADES	ORDER NO.
INDUSTRIAL BLADE NO. 37020 0.20 mm, 10 in magazine	NO. 37020.50
INDUSTRIAL BLADE NO. 36030 0.30 mm, 10 in magazine	NO. 36030.50
INDUSTRIAL BLADE NO. 37030 0.30 mm, 10 in magazine	NO. 37030.50
INDUSTRIAL BLADE NO. 13615 0.15 mm, stainless, 500 blades (each paper-wrapped)	NO. 13615.35
INDUSTRIAL BLADE NO. 13730 0.30 mm, stainless, 10 in transparent pack	NO. 13730.60
INDUSTRIAL BLADE NO. 83715 0.15 mm, stainless, TIN-coated, 100 blades (each paper-wrapped)	NO. 83715.31

» all blades from page 126 onwards

PRODUCT FEATURES NO. 43136.00

Technical features



Main cutting materials



» all cutting materials from page 123 onwards

ACCESSORIES

	ORDER NO.
USED BLADE CONTAINER	NO. 9810.08
WALL MOUNT BRACKET USED BLADE CONTAINER	NO. 9845.06
SAFEBOX	NO. 108000.00

» further information from page 113 onwards

PRODUCT DETAILS

Knife size (L x W x H)	88 x 10.5 x 58 mm
Main material	Plastic
Weight	19.0 g
Weight per unit (self-service card)	31.0 g

ALL MODELS	ORDER NO.
SECUMAX COUPPY with INDUSTRIAL BLADE NO. 36020 1 on self-service card (10 in multipack)	NO. 43136.00

MOUNTABLE BLADES	ORDER NO.
INDUSTRIAL BLADE NO. 36020 0.20 mm, 10 in magazine	NO. 36020.50
INDUSTRIAL BLADE NO. 36013 0.13 mm, 250 blades (each paper-wrapped)	NO. 36013.39
INDUSTRIAL BLADE NO. 36010 0.10 mm, 10 in magazine	NO. 36010.50
INDUSTRIAL BLADE NO. 13615 0.15 mm, stainless, 500 blades (each paper-wrapped)	NO. 13615.35
INDUSTRIAL BLADE NO. 83615 0.15 mm, stainless, TIN-coated, 500 blades (each paper-wrapped)	NO. 83615.35
INDUSTRIAL BLADE NO. 83630 0.30 mm, stainless, TIN-coated, 500 blades (each paper-wrapped)	NO. 83630.35

» all blades from page 126 onwards