


Actuator/Sensor cable, PUR
Bulk Cable
CABLE5x0.34-XX-PUR-OG-100M/TXO

TURCK

Industrial
Automation



- Sheath material: PUR
- Sheath color: orange
- Qualified for drag chain use
- Resistant to weld splatter
- Resistant to chemicals, UV radiation and oils
- Flame retardant
- Free from halogen, silicone, PVC and LABS
- Particularly resistant to abrasion
- Approval: cULus
- RoHS conform
- Protection class IP67
- Cable length: 100 m

Type designation CABLE5x0.34-XX-PUR-OG-100M/TXO
Ident no. 6628626

Number of pins 5

General data

Cable diameter 5.5 ± 0.20mm
 Cable length 100 m
 Cable quality PUR
 Cable color Orange
 Core insulation PP
 Core colors BN, WH, BU, BK, GY
 Core cross-section 5x0.34mm²
 Arrangement of strands 42x0.1 mm


Electrical features at +20 °C

Current 4 A
 Insulation resistance > 30.5 MΩ/km
 Test voltage 2000 V
 Forward resistance max. 57 Ω/km

Mechanical and chemical properties

Max. tensile strength (static) ≤ 50 N/mm²
 Max. tensile strength (dynamic) ≤ 20 N/mm²
 Bending cycles > 5 mil.
 Bending radius (stationary laying) > 5 x Ø
 Bending radius (flexible use) > 10 x Ø
 Admissible acceleration max. 5 m/s²
 Admissible travel path, horizontal 5 m (at 5 m/s²)
 Admissible travel path, vertical 2 m (at 5 m/s²)
 Admissible traversing speed 3.3 m/s
 Torsional stress ± 180 °/m
 Ambient temperature
 Stationary -50...+80°C
 In motion -25...+80°C
 Drag chain operation -25...+60°C

Cable Cross-section





Actuator/Sensor cable, PUR
Bulk Cable
CABLE5x0.34-XX-PUR-OG-100M/TXO

TURCK

Industrial
Automation

Accessories

| Type code | Ident no. | Description | |
|-----------------------------------|-----------|---|---|
| Torque-Wrench-Set-AS | 6936170 | Torque wrench set; handles with adjustable torque 0.4-1.0 Nm, torque wrench for M8 (SW9), fork wrench for M12 (SW 14) |  |
| BLANK-LABEL-FOR-CORDESETS-TEL-TXL | 6936206 | Label for TEL and TXL cables, length: 18 mm, height: 4 mm, material: polycarbonate (PC), color: white, halogen-free and flame-retardant |  |