

**Accessories
IK 16/ZB16 BL****Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

In the switching facilities and controllers, the N conductor may need to be merged with the PE conductor at a central point. For this reason, busbars are available that allow a wide range of cables to be connected within a confined space (up to 70 wires on one metre of rail). The cables are connected via a compression piece or a clamping yoke. For the first variant there is no need to bend the lugs. A guide lug at the compression piece grips into the busbar and holds tightly to the compression piece. The clamping yokes can be moved on the busbar and adjusted to the whole wiring in the facility. The busbar can be used without holes in various lengths. The rail holding clamp SH is used for fastening. On longer rails, it can also be aligned between clamping yokes.

General ordering data

Type	IK 16/ZB16 BL
Order No.	0502980000
Version	Accessories, Special terminal, Rated cross-section: PA, Blue, Busbar
GTIN (EAN)	4008190159696
Qty.	50 pc(s).

Datenblatt

**Accessories
IK 16/ZB16 BL**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	19 mm	Width	9 mm
Height of lowest version	20 mm	Net weight	1.18 g

Temperatures

Operating temperature	Storage temperature
-----------------------	---------------------

Additional technical data

Installation advice	Busbar	Version	15 x 6 mm busbar connection
---------------------	--------	---------	-----------------------------

Material data

Insulating material	PA	Material	Polyamide 66
Colour	Silver	UL 94 flammability rating	V-2

System specifications

Product family	Accessories
----------------	-------------

Classifications

ETIM 3.0	EC000001	UNSPSC	30-21-18-11
eClass 5.1	27-14-11-31	eClass 6.2	27-14-11-90
eClass 7.1	27-14-11-90		

Approvals

Approvals	
ROHS	Conform