

### 3.2x1.6mm SMD CHIP LED LAMP

Part Number: KPTD-3216QBC-D Blue



# **ATTENTION** OBSERVE PRECAUTIONS FOR HANDLING **ELECTROSTATIC**

DISCHARGE SENSITIVE **DEVICES** 

#### **Features**

- 3.2mmX1.6mm SMT LED, 1.8mm thickness.
- Low power consumption.
- Ideal for backlight and indicator.
- Various colors and lens types available.
- Package: 2000pcs / reel .
- Moisture sensitivity level : level 3.
- RoHS compliant.

## Description


The Blue source color devices are made with InGaN Light Emitting Diode.


Static electricity and surge damage the LEDS.

It is recommended to use a wrist band or anti-electrostatic glove when handling the LEDs.

All devices, equipment and machinery must be electrically grounded.

# **Package Dimensions**





- 1. All dimensions are in millimeters (inches).
- 2. Tolerance is  $\pm 0.2 (0.008")$  unless otherwise noted.
- The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.
   The device has a single mounting surface. The device must be mounted according to the specifications.

SPEC NO: DSAA7009 **REV NO: V.16B** DATE: APR/06/2013 PAGE: 1 OF 5 APPROVED: WYNEC CHECKED: Allen Liu DRAWN: Q.M.Chen ERP: 1203002260

## **Selection Guide**

Part No.	Dice	Lens Type	lv (mcd) [2] @ 20mA		Viewing Angle [1]
		2.	Min.	Тур.	201/2
KPTD-3216QBC-D	Blue (InGaN)	Water Clear	300	700	35°

#### Notes:

- $1. \theta 1/2$  is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.
- Luminous intensity/ luminous Flux: +/-15%.
   Luminous intensity value is traceable to the CIE127-2007 compliant national standards.

# Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Blue	460		nm	IF=20mA
λD [1]	Dominant Wavelength	Blue	465		nm	IF=20mA
Δλ1/2	Spectral Line Half-width	Blue	25		nm	IF=20mA
С	Capacitance	Blue	100		pF	VF=0V;f=1MHz
VF [2]	Forward Voltage	Blue	3.3	4	V	IF=20mA
lr	Reverse Current	Blue		50	uA	V <sub>R</sub> =5V

### Notes:


- 1.Wavelength: +/-1nm.
- 2. Forward Voltage: +/-0.1V.
- 3. Wavelength value is traceable to the CIE127-2007 compliant national standards.

# Absolute Maximum Ratings at TA=25°C

Parameter	Blue	Units	
Power dissipation	120	mW	
DC Forward Current	30	mA	
Peak Forward Current [1]	150	mA	
Reverse Voltage	5	V	
Operating Temperature	-40°C To +85°C		
Storage Temperature	-40°C To +85°C		

Note: 1. 1/10 Duty Cycle, 0.1ms Pulse Width.

SPEC NO: DSAA7009 **REV NO: V.16B** DATE: APR/06/2013 PAGE: 2 OF 5 APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: Q.M.Chen ERP: 1203002260




 SPEC NO: DSAA7009
 REV NO: V.16B
 DATE: APR/06/2013
 PAGE: 3 OF 5

 APPROVED: WYNEC
 CHECKED: Allen Liu
 DRAWN: Q.M.Chen
 ERP: 1203002260

### KPTD-3216QBC-D

Reflow soldering is recommended and the soldering profile is shown below. Other soldering methods are not recommended as they might cause damage to the product.

Reflow Soldering Profile For Lead-free SMT Process.




- NOTES:

  1.We recommend the reflow temperature 245°C(+/-5°C). The maximum soldering temperature should be limited to 260°C.


  2.Don't cause stress to the epoxy resin while it is exposed to high temperature.

  3.Number of reflow process shall be 2 times or less.


# **Recommended Soldering Pattern** (Units: mm; Tolerance: ± 0.1)



## **Reel Dimension**




**Tape Dimensions** (Units: mm)





SPEC NO: DSAA7009 **REV NO: V.16B** DATE: APR/06/2013 PAGE: 4 OF 5 **APPROVED: WYNEC CHECKED: Allen Liu** DRAWN: Q.M.Chen ERP: 1203002260

## **PACKING & LABEL SPECIFICATIONS**

### KPTD-3216QBC-D







Detailed application notes are listed on our website. <a href="http://www.kingbright.com/application">http://www.kingbright.com/application</a> notes

SPEC NO: DSAA7009 APPROVED: WYNEC REV NO: V.16B CHECKED: Allen Liu DATE: APR/06/2013 DRAWN: Q.M.Chen PAGE: 5 OF 5 ERP: 1203002260