



For more Information
please call

1-800-Belden1



General Description:

28 and 24 AWG stranded TC conductors, non-plenum, Polypropylene insulation, twisted pairs, overall polyester isolation tape + Duofoil® + TC braid shield (92% coverage), drain wire, light gray PVC jacket.

Usage (Overall)

Suitable Applications: IEEE 802.3 Transceiver Cable

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
3	28	7x36	TC - Tinned Copper
1	24	7x32	TC - Tinned Copper

Total Number of Conductors: 8

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)	AWG
PP - Polypropylene	0.009	28
PP - Polypropylene	0.010	24

Inner Shield

Inner Shield Material:

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil® (Z-Fold®)	Tape	Aluminum Foil-Polyester Tape	100

Inner Shield Drain Wire AWG:

AWG
24

Inner Shield Drain Wire Stranding: 7x32

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	92

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	0.033

Overall Cable

Overall Cabling Separator Material: Polyester Tape

Overall Nominal Diameter: 0.250 in.

Pair

Pair Color Code Chart:

Number	Color
78 Ohm	Gray & White
78 Ohm	Yellow & Orange
78 Ohm	Blue & Green
Power Pair	Black & Red

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +80°C

UL Temperature Rating: 80°C (UL AWM Style 2919)

Bulk Cable Weight:	39 lbs/1000 ft.
Max. Recommended Pulling Tension:	68 lbs.
Min. Bend Radius/Minor Axis:	2.500 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMG
CEC/C(UL) Specification:	CMG
AWM Specification:	UL Style 2919 (30 V 80°C)
IEEE Specification:	IEEE802.3
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

CSA Flame Test:	FT4
-----------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)	Tolerance (Ohms)
78	± 5

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
19.7

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)
34.8

Nominal Velocity of Propagation:

VP (%)
66

Nominal Delay:

Delay (ns/ft)
1.54

Nom. Conductor DC Resistance:

Description	DCR @ 20°C (Ohm/1000 ft)
28 AWG	65
24 AWG	24

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
2.9

Max. Operating Voltage - UL:

Voltage	Description
30 V RMS	UL AWM Style 2919
300 V RMS	CMG

Max. Recommended Current:

Current
.875 Amps per conductor at 25°C (28 AWG); 1.5 Amps per conductor at 25°C (24 AWG)

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9903 E4X1000	1,000 FT	43.000 LB	GRAY, LIGHT DEC	C	1#24,3#28 SHPR PP SH PVC
9903 E4X500	500 FT	21.500 LB	GRAY, LIGHT DEC		1#24,3#28 SHPR PP SH PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 11-07-2012

© 2017 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).