


Ascent 150 II Round Aluminium Reflector

ASCENT 150 II 3700 4K DALI
2059369



Product features

- The ASCENT 150 II 3700 4K DALI is a high efficient downlight luminaire, Colour rendering index Ra >80, Colour temperature: 4000K Neutral White, Class II, Protection rating IP44/IK03



PRODUCT OVERVIEW

Product name	ASCENT 150 II 3700 4K DALI
Technology	LED
Cap/Base	N/A
Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	Internal
General application	Hospitality, Office, Retail
ETIM Class	EC001744
E-number FI	4237886
Warranty	5 years
Fixture luminous flux (lm)	3700
Luminaire efficacy (lm/W)	137
LOR (%)	100
Colour temperature (K)	4000
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Colour Consistency (SDCM)	3
Beam Angle (°)	80
Glare control	< 23
Photobiological Risk Group	RG0
Total power consumption (W)	27
Electrical protection	Class II
Control gear type	Electronic ballast
Dimmable	Yes
Dimming method	DALI, Switch-dim (mains-rated)
Minimum dimming level (%)	1
Housing colour	RAL 9016 - Traffic white / Bezel
IP rating	IP44/20
IK rating	IK03
Product EAN number	5025768593699

Ascent 150 II Round Aluminium Reflector

ASCENT 150 II 3700 4K DALI
2059369

DATA TABLE

General data

Product name	ASCENT 150 II 3700 4K DALI
Technology	LED
Cap/Base	N/A
Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	Internal
General application	Hospitality, Office, Retail
Operating temperature range (°C)	25°C...+25°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001744
E-number FI	4237886
Warranty	5 years

Optical data

Fixture luminous flux (lm)	3700
Luminaire efficacy (lm/W)	137
LOR (%)	100
Colour temperature (K)	4000
Correlated colour temperature range (K)	4000 - 4000
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Colour Consistency (SDCM)	3
Adjustable chromaticity	N
Beam Angle (°)	80
Distribution type	Diffuse
Glare control	< 23
Photobiological Risk Group	RG0

Electrical data

Total power consumption (W)	27
Mains voltage (V)	220-240V
Lamp power factor	1
THD (at 230 V, 50 Hz, full load, at 100% dimming level) xx.x %	7
Electrical protection	Class II
Control gear type	Electronic ballast
Transformer required	Yes
Dimmable	Yes
Dimming method	DALI, Switch-dim (mains-rated)
Minimum dimming level (%)	1
Drive current (mA)	1000
Inrush Current (A)	25
Inrush Duration (µs)	141
Glow Wire Test (°C)	650

Ascent 150 II Round Aluminium Reflector

ASCENT 150 II 3700 4K DALI
2059369

Energy Efficiency Class (A->G) of contained light source	B
Nominal Frequency (Hz)	50/60/HF
Max. Luminaires per 10A C Breaker	31
Max. Luminaires per 13A C Breaker	40
Max. Luminaires per 16A C Breaker	51
Max. Luminaires per 20A C Breaker	66
Max. Luminaires per 10A B Breaker	19
Max. Luminaires per 13A B Breaker	24
Max. Luminaires per 16A B Breaker	31
Max. Luminaires per 20A B Breaker	40

Lifetime data

Lifespan L70 B50	100000
Lifespan L80 B20	100000
Lifespan L90 B10	55000

Physical data

Housing colour	RAL 9016 - Traffic white / Bezel
IP rating	IP44/20
IK rating	IK03
Diffuser finish	Transparent
Diffuser material	PC Polycarbonate
Reflector finish	Other
Nominal Product Width (mm)	189
Nominal Product Height (mm)	107
Nominal Product Diameter (mm)	189
Cutout Dimensions (W x L in mm or Diameter in mm)	176
Weight (kg)	1.03
Recessed Depth (mm)	120

Packaging


Single packaging type	Carton
Product EAN number	5025768593699
Packaging single length / height (cm)	25.0
Packaging single width (cm)	20.0
Packaging single depth (cm)	25.0
DUN14 (outer)	05025768593699
Units per outer package	1
Packaging outer length / height (cm)	25.0
Packaging outer width (cm)	20.0
Packaging outer depth (cm)	25.0

Safety data

Optimal operating condition (°C)	25-25
----------------------------------	-------

Ascent 150 II Round Aluminium Reflector *ASCENT 150 II 3700 4K DALI* 2059369

PHOTOMETRY



0.5	0.90	E(0°) E(C0)	42.1°	7645 1798
1.0	1.81	E(0°) E(C0)	42.1°	1911 448
1.5	2.71	E(0°) E(C0)	42.1°	849 198
2.0	3.61	E(0°) E(C0)	42.1°	478 112
2.5	4.52	E(0°) E(C0)	42.1°	306 71
3.0	5.42	E(0°) E(C0)	42.1°	212 50

Distance [m] Cone diameter [m] Illuminance [lx]
 C0 - C180 (Half beam angle: 64.2°)

TECHNICAL DRAWINGS

