




**MORSETTIERE PER C.S.**  
**TERMINAL BLOCKS FOR P.C.B.**  
**BARRETTES DE CONNEXION POUR C.I.**  
**ANSCHLÜßKLEMMEN FÜR LEITERPLATTE**

TIPO  
 TYPE  
 TYPE  
 TYP


**MRT8**

PASSO  
 PITCH  
 PAS  
 RASTERMAß

**3,5 3,81 mm**



MRT8 P3,81 / ...



P	L mm
3,5	3,5 x p
3,81	3,81x p-5

CONNETTORE FEMMINA  
 A MODULI

FEMALE CONNECTOR  
 MODULES

CONNECTEUR FEMELLE  
 ELEMENTS

BUCHSENLEISTE  
 ANREIHBAR



Corpo isolante Verde	Insulating body Green	Corps isolant Vert	Isolierkörper Grün	
Vite	Screw	Vis	Schraube	PA68 UL94VO
Morsetto	Clamp	Borne	Klemmkörper	M2-CB4FF+Zn
Contatto	Pin	Contacte	Kontakt	Cu Zn40 Pb2+Ni
Coppia di torsione	Testing torque	Couple de serrage	Zul. Drehmoment	CuSn7+Ni
Sezione	Section	Section	Querschnitt	0,4 Nm
Vite imperdibile	Captive screw	Vis imperdable	Schraube unvelierbar	1 mm <sup>2</sup>
Foro di montaggio	P.C.B. mounting hole	Perçage C. I.	Leiterplattenbohrung	-
Corrente nominale	Nominal current	Courant nominal	Strombelastbarkeit	9A
Tensione	Voltage	Tension	Betriebsspannung	130/450 V
Temperatura	Temperature	Température	Temperatur	85°C
Grado di protezione	Protection index	Degré de protection	Schutzklasse	IP00
Resistenza di isolamento	Insulation resistance	Résistance d'isolement	Isolationswiderstand	≥ 5 MΩ
Rigidità dielettrica	Dielectric strength	Rigidité diélectrique	Durchschlagsfestigkeit	≥ 1250 Vac/60"

Ref. EN 60998-1

SCHEMA PER ORDINAZIONE	ORDER SCHEME	TABLEAU DE COMMANDE	BESTELLSCHHEMA
	P	p	
	Passo	N° di Poli	Numerazione
	Pitch	Nr. of Poles	Printing
	Pas	Nb. Pôles	Marquage
	Rastermaß	Polzahl	Bedruckung
	3,5 3,81	MIN 2÷ MAX 20	
<b>MRT8</b>	P ... / ...		<b>NU</b>




**MORSETTIERE PER C.S.**  
**TERMINAL BLOCKS FOR P.C.B.**  
**BARRETTES DE CONNEXION POUR C.I.**  
**ANSCHLUßKLEMMEN FÜR LEITERPLATTE**

TIPO  
 TYPE  
 TYPE  
 TYP




**MRT9**

PASSO  
 PITCH  
 PAS  
 RASTERMAß

**3,5 3,81 mm**




MRT9 P3,81/...



P	L mm
3,5	3,5 x p+1,4
3,81	3,81 x p+1,39

MRT9 P3,81/...SQ



CONNETTORE MASCHIO  
 A MODULI CHIUSI  
 E APERTI

MALE CONNECTOR  
 CLOSED AND OPENED  
 MODULES

CONNECTEUR MALE  
 ELEMENTS CLOISSONNE  
 OU NON CLOISSONNE

STECKER  
 BAUSTEINE SEITLICH  
 GESCHLOSSEN ODER OFFEN



Corpo isolante Verde	Insulating body Green	Corps isolant Vert	Isolierkörper Grün	PA68 UL94V0
Contatto	Pin	Borne	Kontakt	CuSn7+Sn
Foro di montaggio	P.C.B. mounting hole	Perçage C. I.	Leiterplattenbohrung	Ø 1,3 mm
Corrente nominale	Nominal current	Courant nominal	Strombelastbarkeit	9 A
Tensione	Voltage	Tension	Betriebsspannung	130/450 V
Temperatura	Temperature	Température	Temperatur	85°C
Grado di protezione	Protection index	Degré de protection	Schutzklasse	IP00
Resistenza di isolamento	Insulation resistance	Résistance d'isolement	Isolationswiderstand	≥ 5 MΩ
Rigidità dielettrica	Dielectric strength	Rigidité diélectrique	Durchschlagsfestigkeit	≥ 1250 Vac/60"

Ref. EN 60998-1

SCHEMA  
 PER ORDINAZIONE

ORDER  
 SCHEME

TABLEAU  
 DE COMMANDE

BESTELLSCHHEMA

P	p	
Passo	N° di Poli	Numerazione
Pitch	Nr. of Poles	Printing
Pas	Nb. Pôles	Marquage
Rastermaß	Polzahl	Bedruckung
3,5 3,81	MIN 2÷ MAX 20	Pin 90°
MRT9	P ... / ...	NU