

DVJN insert holder, negative left

For contour and longitudinal turning with VN indexable insert



Application:

For contour and longitudinal turning with VN indexable insert, 35°

Execution:

- Precision-manufactured steel support, burnished, hardened, adjustable clamping system, type V, pitch angle 93°, tip angle 35°, clearance angle 0°

Advantage:

- Streamlined geometry, optimised for contour lathe work with high feed depths and unfavourable conditions
- Negative body geometry ensures good stability and absorption of force for large cutting depths
- Wide adjustment range: Suitable for both finishing and rough machining
- Adjustable clamp minimises vibrations and ensures favourable power transmission

Art. no.	17684 105
Brand	WIDIA
Manufacturer Part Number	5696732
ISO name	DVJN R/L 2020 K16
Knife edge length	16 mm
Shaft height	20 mm
Shank width	20 mm
Length	125 mm
Programming size	25 mm
Suitable for indexable inserts	VN.. 2204..
Tool design	Left
Length of head	46 mm
Gross Weight	0.045 kg
Product Group	1XG

EAN

4050841486705