


# AC2753



## AS-Interface PCB module

PCB 4DI 3DO T C A/B



Electrical data	
Operating voltage [V]	18...31.6 DC
Max. current consumption from AS-i [mA]	180; (without sensors: < 30 mA; inputs and outputs active: < 180 mA)
Protection class	III
Max. current load total [A]	0.15; (total current for all outputs and sensor supply supplied from AS-i: 150 mA)
Integrated watchdog	yes
Inputs / outputs	
Number of inputs and outputs	Number of digital inputs: 4; Number of digital outputs: 3
Inputs	
Number of digital inputs	4
Input circuit of digital inputs	PNP
Sensor supply of the inputs	AS-i
Voltage supply [V]	18...30
Max. total current rating of inputs [mA]	150
Input current High [mA]	6...10
Input current Low [mA]	0...2
Min. switching level high signal [V]	11
Digital inputs protected against short circuits	yes
Outputs	
Number of digital outputs	3
Circuit	PNP
Voltage range DC [V]	AS-i
Max. current load per output [mA]	100; (utilisation category DC-13 (control of electromagnets): 2,5 W (IEC 60947-5-1))
Short-circuit proof	yes
Electrically separated	yes
Operating conditions	
Ambient temperature [°C]	-25...55
Protection	IP 20
Tests / approvals	
EMC	EN 50295



## AS-Interface PCB module

PCB 4DI 3DO T C A/B

AS-i classification		
AS-i version	3.0	
Extended addressing mode possible	yes	
AS-i profile	S-7.A.E	
AS-i I/O configuration [hex]	7	
AS-i ID code [hex]	A.E	
AS-i certificate	102401	
Mechanical data		
Weight [g]	68	
Type of mounting	installation in a surface-mounted housing	
Dimensions [mm]	31.1 x 12 x 76.6	
Materials	housing: PC potted	
Displays / operating elements		
Display	operation	LED, green
	errors	LED, red
	function	LED, yellow
Remarks		
Remarks	A watchdog function switches the outputs off if there is no communication on the AS-i line.	
	Install the unit so that exposed parts cannot be touched.	
	Installation in a surface-mounted housing with the dimensions of 68 x 136 x 53 mm (LxWxH), e.g. Schneider Electric Harmony, XALD03, XALD04	
	Do not connect any of the following points to an external potential:	
	0-, I+, I1, I2, I3, I4	
The connections are electrically connected with the AS-i cable.		
can be used up to a height of 2000 metres above sea level		
Pack quantity	1 pcs.	
Electrical connection		
screw terminals:		
I1	switching input sensor 1	
I2	switching input sensor 2	
I3	switching input sensor 3	
I4	switching input sensor 4	
O1	switching output actuator 1	
O2	switching output actuator 2	
O3	switching output actuator 3	
0-	sensor and actuator supply 0 V	
I+	sensor and actuator supply 24 V	
AS-i - (FLT)	AS-i -	
AS-i + (PWR)	AS-i +	