

3-828102-1 ✓ ACTIVE

AMPLIMITE | AMPLIMITE Kit


TE Internal #: 3-828102-1

AMPLIMITE Kit, D-Sub Locking & Mounting, Female Screwlocks,  
Screw Length .36 in [9.2 mm]

[View on TE.com >](#)



Connectors > D-Shaped Connectors > D-Sub Accessories > Locking & Mounting



D-Shaped Connector Accessories: **Female Screwlocks**

Screw Length: **9.2 mm [ .36 in ]**

## Features

### Product Type Features

Product Type	Accessory
D-Shaped Connector Accessories	Female Screwlocks

### Mechanical Attachment

Screwlock Style	Screwlock Only
Mating Thread Size	14702
Screw & Hole Thread Size	4-40 UNC 2A (Male), 4-40 UNC 2B (Female)
Screw Length	9.2 mm[.36 in]

### Dimensions

Thread Length	3 mm[.118 in]
---------------	---------------

### Packaging Features

Packaging Quantity	2000
Packaging Method	Carton

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
------------------------------	---------------------------



EU ELV Directive 2000/53/EC

Not Yet Reviewed

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2021 (211)  
 Candidate List Declared Against: JAN 2021 (211)  
 SVHC > Threshold:  
 Pb (3.5% in Component Part)  
**Article Safe Usage Statements:**  
 Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free


Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



Also in the Series | **AMPLIMITE Kit**



D-Sub Backshells & Clamps(136)



D-Sub Contact Accessories(1)



D-Sub Covers(3)



D-Sub Locking & Mounting(122)

## Customers Also Bought



TE Part #1-338309-2  
D-Sub Plug Assembly: Standard, Vertical, Shell Size 1, 2.74mm



TE Part #176976-1  
AMP UNIVERSAL POWER PLG 3C PCB




TE Part #1676170-2  
RN 0805 127K 0.1% 10PPM 1KRL



TE Part #1676222-3  
RN 0805 1K13 0.1% 10PPM 5KRL



TE Part #1676295-2  
RN 0805 2K87 0.1% 10PPM 1KRL



TE Part #1496476-2  
STD USB-A TO MINI-B ASSY 1.5M



TE Part #87175-6  
02 LOCKING CLIP HSG SR .100CL



TE Part #1-487576-2  
20 ZIFLINE 50 ASSY



TE Part #104350-3  
06 MODII HDR DRST B/A W/HD



TE Part #1-1649328-0  
RT314005

## Documents

### Product Drawings

[HD-20SCHRAUB-SICHRG](#)

English

### CAD Files

[3D PDF](#)

3D

[Customer View Model](#)

[ENG\\_CVM\\_CVM\\_3-828102-1\\_J.2d\\_dxf.zip](#)



English

Customer View Model

[ENG\\_CVM\\_CVM\\_3-828102-1\\_J.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_3-828102-1\\_J.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

**Product Environmental Compliance**

**TE Material Declaration**

English