



DICHT-BECHERBLINDNIETE
SENKKOPF 120°

SEALED BLIND RIVETS
COUNTERSUNK HEAD 120°


RIVETS ÉTANCHES
TÊTE FRAISÉE 120°










Aluminium Legierung [AlMg 5]
Aluminium alloy [AlMg 5]
Aluminium alliage [AlMg 5]


Edelstahl A2 [1.4301]
Stainless steel A2 [AISI 304]
Acier inox A2 [1.4301]








Ø 3,2 mm

D1 = 3,2 +/- 0,08 mm
D2 = 6,0 +/- 0,4 mm
k = -
d = 1,7 mm
P ≥ 27,0 mm
L = + 1,0 / - 0,2 mm
 3,3 mm


						
3,2 x 7,5 mm	1,5 - 3,0 mm	21211 32750	1050 N	1200 N	1000	10000
3,2 x 9,0 mm	3,0 - 4,5 mm	21211 32900			1000	10000
3,2 x 10,5 mm	4,5 - 6,5 mm	21211 32105			1000	10000








Ø 4,0 mm

D1 = 4,0 +/- 0,08 mm
D2 = 7,5 +/- 0,5 mm
k = -
d = 2,2 mm
P ≥ 27,0 mm
L = + 1,0 / - 0,2 mm
 4,1 mm

						
4,0 x 9,5 mm	2,0 - 5,0 mm	21211 40950	1550 N	2100 N	500	5000
4,0 x 11,0 mm	5,0 - 6,5 mm	21211 40110			500	5000
4,0 x 12,5 mm	6,0 - 8,0 mm	21211 40125			500	5000

Ø 4,8 mm

D1 = 4,8 +/- 0,08 mm
D2 = 9,5 +/- 0,5 mm
k = -
d = 2,65 mm
P ≥ 27,0 mm
L = + 1,0 / - 0,2 mm
 4,9 mm

						
4,8 x 9,5 mm	2,5 - 4,5 mm	21211 48950	2100 N	3000 N	250	2500
4,8 x 11,0 mm	4,5 - 6,0 mm	21211 48110			250	2500
4,8 x 12,5 mm	6,0 - 7,5 mm	21211 48125			250	2500
4,8 x 14,0 mm	7,5 - 9,0 mm	21211 48140			250	2500
4,8 x 15,5 mm	9,0 - 10,5 mm	21211 48155			250	2500
4,8 x 17,0 mm	10,5 - 12,0 mm	21211 48170			250	2500
4,8 x 19,0 mm	12,0 - 14,0 mm	21211 48190			250	2500