




Hydrostatic submersible pressure transmitter

SUBMERSIBLE 0,25BAR 5M FEP CABLE



Product characteristics				
Output signal	analogue signal			
Measuring range	0...0.25 bar	0...250 mbar	0...3.63 psi	0...25 kPa
Application				
Design	with capillary tube for pressure compensation			
Application	for industrial applications			
Media	Liquids			
Medium temperature [°C]	-10...85			
Pressure rating	2 bar	29 psi	200 kPa	
Min. bursting pressure	2.4 bar	35 psi	240 kPa	
Type of pressure	relative pressure			
Electrical data				
Operating voltage [V]	10...30 DC			
Protection class	III			
Reverse polarity protection	yes			
Inputs / outputs				
Number of inputs and outputs	Number of analogue outputs: 1			
Outputs				
Total number of outputs	1			
Output signal	analogue signal			
Number of analogue outputs	1			
Analogue current output [mA]	4...20			
Max. load [Ω]	700; (U _b = 24 V; (U _b - 10 V) / 20 mA)			
Short-circuit protection	yes			
Measuring/setting range				
Measuring range	0...0.25 bar	0...250 mbar	0...3.63 psi	0...25 kPa
Accuracy / deviations				
Repeatability [% of the span]	< 0,1; (with temperature fluctuations < 10 K)			
Characteristics deviation [% of the span]	< 0,25 (BFSL) / 0,5; (incl. linearity, zero and span error (limit value setting))			
Linearity deviation [% of the span]	< 0,2 (BFSL)			
Long-term stability [% of the span]	< 0,2; (per year)			
Temperature coefficient zero point	< ± 0,2; (0...50 °C)			

PS4208



Hydrostatic submersible pressure transmitter

SUBMERSIBLE 0,25BAR 5M FEP CABLE

[% of the span / 10 K]	
Temperature coefficient span [% of the span / 10 K]	< ± 0,2; (0...50 °C)

Operating conditions	
Ambient temperature [°C]	-10...85
Storage temperature [°C]	-30...80
Protection	IP 68


Tests / approvals	
MTTF [years]	403
Pressure Equipment Directive	Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request

Mechanical data	
Weight [g]	584.2
Materials	stainless steel (1.4571/316Ti); PA

Remarks	
Pack quantity	1 pcs.

Electrical connection	
Cable: 5 m, FEP, Ø 7.5 mm	

Connection



1: screen (connected to the housing)

Core colours :

BN = brown

GN = green