

Shrink-fit chuck, slimline, 3 degrees

For mould making with minimum interference contour

ATORN[®]

Application

For clamping cutters and drills with straight shanks in h6 tolerance. Suitable for heavy-duty machining and all high-power applications. Suitable for inductive, contact and hot air shrinking devices.

Version

- Guaranteed maximum concentricity 0.003 mm
- For shrinking cemented carbide and HSS tools in and out
- Hardness 52 + 2 HRC
- Maximum coolant pressure 80 bar
- glass bead blasted

Advantage

- Slimline design, extremely low interference contour
- High transmittable torques
- High positioning and repeat accuracy
- Ideal for high rotation speeds



Art. no.	23427 310
Clamping diameter	10 mm
Tapered diameter	16 mm
Outer diameter	22 mm
Projecting length	90 mm
Max. clamp in depth	41 mm
Suitable for thread	M8 x 1
Width across flats	3 mm
Max. adjustment travel	10 mm
Balancing quality	G 2.5 at 25 rpm

EAN-Code

4050293409352