

<b>Product type designation</b>	<b>RUGGEDCOM Media Module CG01</b>
Product description	2 x 10/100/1000 Tx RJ45 RUGGEDCOM MEDIA MODULE GIGABIT COPPER MEDIA MODULE CG01 (2X10/100/1000TX RJ45). ONLY FOR RSG22XX AND RSG2300. EQUIVALENT TO CG01
Suitability for operation	For RSG2100 only

### Interfaces

Number of electrical/optical connections / for network components or terminal equipment / maximum	2
Number of electrical connections <ul style="list-style-type: none"> <li>• for network components or terminal equipment / maximum</li> </ul>	2
Number of 10/100/1000 Mbit/s RJ45 ports	2
Type of electrical connection <ul style="list-style-type: none"> <li>• for network components or terminal equipment</li> </ul>	RJ45

### Permitted ambient conditions

Ambient temperature <ul style="list-style-type: none"> <li>• during operation</li> <li>• during storage</li> <li>• during transport</li> <li>• Note</li> </ul>	-40 ... +85 °C -40 ... +85 °C -40 ... +85 °C A maximum ambient operating temperature of +85 °C is permissible for a duration of 16 hours
Relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
Protection class IP	IP20

### Design, dimensions and weight

Design	Media module
Coating	Conformal Coating
Mounting type <ul style="list-style-type: none"> <li>• Installation in media module slot</li> </ul>	screwed Yes

### Standards, specifications, approvals

Standard <ul style="list-style-type: none"> <li>• for EMC</li> <li>• for safety / from CSA and UL</li> <li>• for hazardous zone / from CSA and UL</li> <li>• for emitted interference</li> <li>• for interference immunity</li> </ul>	FCC Part 15 (Class A), EN55022 (CISPR22 Class A) UL 60950-1, CSA C22.2 No. 60950-7 Hazardous Locations: Class 1 Division 2 EN 61000-6-4 (Class A) EN 61000-6-2
Certificate of suitability	EN 61000-6-2, EN 61000-6-10

- CE marking
- C-Tick
- KC approval
- E1 approval
- IEC 61850-3

Yes  
No  
No  
No  
Yes

## Further Information / Internet Links

### Internet-Link

- to website: Industry Mall/RUGGEDCOM selector
- to website: Siemens RUGGEDCOM
- to website: Selector for cables and connectors
- to website: Industrial communication
- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAx Download Manager
- to website: Industry Online Support

<http://ruggedcom-selector.automation.siemens.com>

<http://siemens.com/ruggedcom>

<http://www.siemens.com/snst>

<http://www.siemens.com/simatic-net>

<https://mall.industry.siemens.com>

<http://www.siemens.com/automation/net/catalog>

<http://automation.siemens.com/bilddb>

<http://www.siemens.com/cax>

<https://support.industry.siemens.com>

**last modified:**

16.03.2015