



Part Number: 4855ANH

12 GHz Coax, 4K UHD Precision Video Coax, RG-59 Mini, 75 Ohm, 23 AWG Solid

Product Description

12 GHz Coax, 4K UHD Precision Video Cable, RG-59 Mini, 75 Ohm, 23 AWG solid .023" silver plated copper conductor, gas-injected foam HDPE insulation, Duofoil® bonded to the core + tinned copper braid shield (95% coverage), LSZH jacket.

Technical Specifications

Product Overview

Environmental Space:	Indoor - Euroclass Dca
Suitable Applications:	SMPTE 2082-1 12 Gb/s UHD TV, SMPTE 2081-1 6 Gb/s UHD TV, SMPTE 424M 3 Gb/s HD-SDI 1080P

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
23	Solid	SPC - Silver Plated Copper	0.023 in	1

Conductor Size:	23 AWG
-----------------	--------

Insulation

Material	Nominal Diameter
Gas-injected FHDPE - Foam High Density Polyethylene	0.102 in

Outer Shield Material

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Aluminum / Polyester / Aluminum	Bonded Duofoil® (Bonded to Dielectric)	100.0 %
Braid	2	TC - Tinned Copper		95.0 %

Outer Jacket Material

Material	Nominal Diameter
LSZH / FRNC	0.159 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Outer Conductor DCR
19.7 Ohm/1000ft	3.9 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Shield
16.3 pF/ft

Inductance

Nominal Inductance
0.107 µH/ft

Impedance

Nominal Characteristic Impedance
75 Ohm

Return Loss (RL)

Frequency [MHz]	Minimum Return (RL)
5 MHz - 1600 MHz	23 dB
1600 MHz - 4500 MHz	21 dB
4500 MHz - 12000 MHz	15 dB

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz MHz	0.39 dB/100ft
3.58 MHz MHz	0.78 dB/100ft
5 MHz MHz	0.92 dB/100ft
6 MHz MHz	1 dB/100ft
7 MHz MHz	1.08 dB/100ft
10 MHz MHz	1.2 dB/100ft
12 MHz MHz	1.3 dB/100ft
25 MHz MHz	1.8 dB/100ft
55 MHz MHz	2.6 dB/100ft
67.5 MHz MHz	2.83 dB/100ft
71.5 MHz MHz	2.93 dB/100ft
88.5 MHz MHz	3.22 dB/100ft
100 MHz MHz	3.39 dB/100ft
135 MHz	3.84 dB/100ft
143 MHz	4.00 dB/100ft
180 MHz	4.41 dB/100ft
270 MHz	5.44 dB/100ft
360 MHz	6.34 dB/100ft
540 MHz	7.85 dB/100ft
720 MHz	9.09 dB/100ft
750 MHz	9.28 dB/100ft
1000 MHz	10.8 dB/100ft
1500 MHz	13.2 dB/100ft
2000 MHz	15.3 dB/100ft
2250 MHz	16.3 dB/100ft
3000 MHz	19.0 dB/100ft
4500 MHz	23.6 dB/100ft
6000 MHz	27.7 dB/100ft
12000 MHz	41.2 dB/100ft

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.24 ns/ft	82.0 %

Voltage

Non-UL Voltage Rating
300 V RMS

Electrical Characteristics Notes:	Return Loss: Fixed bridge and termination
Other Electrical Characteristic 2:	Percent test

Temperature Range

UL Temp Rating:	75°C
Operating Temp Range:	-30°C To +75°C

Mechanical Characteristics

UV Resistance:	Yes
Bulk Cable Weight:	17 lbs/1000ft
Max Recommended Pulling Tension:	40 lbs
Min Bend Radius/Minor Axis:	1.6 in

Standards

CPR Euroclass:	Dca
----------------	-----

RG Type:	Mini 59/U Type
----------	----------------

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes

Suitability

Suitability - Aerial:	Yes - Black only, when supported by messenger wire
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes - Black only

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	UPC	Length
4855ANH G751000	Aqua	612825443353	305 m
4855ANH G751640	Aqua	612825443407	500 m
4855ANH G753280	Aqua	612825443452	1,000 m
4855ANH G751000	Aqua		305 m
4855ANH G751640	Aqua		500 m
4855ANH G753280	Aqua		1,000 m
4855ANH 0101000	Black	612825443391	305 m
4855ANH 0101640	Black	612825443445	500 m
4855ANH 0103280	Black	612825443490	1,000 m
4855ANH 0101000	Black		305 m
4855ANH 0101640	Black		500 m
4855ANH 0103280	Black		1,000 m
4855ANH 0061000	Blue	612825443377	305 m
4855ANH 0061640	Blue	612825443421	500 m
4855ANH 0063280	Blue	612825443476	1,000 m
4855ANH 0061000	Blue		305 m
4855ANH 0061640	Blue		500 m
4855ANH 0063280	Blue		1,000 m
4855ANH N3U1000	Green	612825443360	305 m
4855ANH N3U1640	Green	612825443414	500 m
4855ANH N3U3280	Green	612825443469	1,000 m
4855ANH N3U1000	Green		305 m
4855ANH N3U1640	Green		500 m
4855ANH N3U3280	Green		1,000 m
4855ANH 0071000	Purple	612825443384	305 m
4855ANH 0071640	Purple	612825443438	500 m
4855ANH 0071000	Purple		305 m
4855ANH 0071640	Purple		500 m
4855ANH 0073280	Purple		1,000 m

Product Notes

Notes:	Print legend includes sequential footage marks.
--------	---

History

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.