

## DIAPOINT single-diamond dressing tools with 3-5 natural points, few impurities (2nd. quality)

For dressing ceramic grinding wheels




### Application:

Suitable for all machines with corresponding holder. **Chucking:** Inclination of dressing tool to sanding disc centre from 5° to 15° required. We recommend **selecting the appropriate diamond weight** for individual diamond dressing tools according to the following diagram depending on the sanding disc to be adjusted.

### Version:

- Universal, traditional dressing tool with a single diamond with protruding working tip



|   |                  |
|---|------------------|
| <b>Art. no.</b>                           | <b>61135 050</b> |
| <b>Shank style</b>                        | Morse taper      |
| <b>Morse taper size</b>                   | MK 0             |
| <b>Natural tip quality</b>                | 2                |
| <b>Weight of diamond</b>                  | 0.5 carat        |
| <b>Min./max. side feed per revolution</b> | 0.05-0.15 m/s    |
| <b>Min./max supply per throughput</b>     | 0.01-0.03 mm     |
| <b>Number of pieces per packet</b>        | 1 PCS            |
| <b>DIN</b>                                | 228              |