

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**Myxal HDS**

Revision date: 30.11.2022

Product code: 00320-0220-GHS

Page 1 of 9

**SECTION 1: Identification of the substance/mixture and of the company/undertaking****1.1. Product identifier**

Myxal HDS

**1.2. Relevant identified uses of the substance or mixture and uses advised against****Use of the substance/mixture**

Hygienic hand washing

**1.3. Details of the supplier of the safety data sheet**

Company name:	Peter Greven Physioderm GmbH	
Street:	Procter-&-Gamble-Str. 26	
Place:	53881 Euskirchen	
Telephone:	+49 (2251) 77 617-0	Telefax: +49 (2251) 77 617-44
e-mail:	info@pgp-hautschutz.de	
Responsible Department:	Responsible for the safety data sheet: sds@gbk-ingelheim.de	

**1.4. Emergency telephone number:**INTERNATIONAL: +49 - (0) 6132 - 84463, GBK GmbH (24h - 7d/w - 365d/a)  
In England and Wales: NHS 111 In Scotland: NHS 24 - dial 111**SECTION 2: Hazards identification****2.1. Classification of the substance or mixture****Regulation (EC) No. 1272/2008**

Hazard categories:

Hazardous to the aquatic environment: Aquatic Chronic 3

Hazard Statements:

Harmful to aquatic life with long lasting effects.

**2.2. Label elements****Regulation (EC) No. 1272/2008****Hazard statements**

H412 Harmful to aquatic life with long lasting effects.

**Precautionary statements**

P273 Avoid release to the environment.

P501 Dispose of contents/container to approved disposal company or local collection.

**2.3. Other hazards**

According to Regulation (EC) No 1907/2006 (REACH) none of the substances, contained in this product are a PBT / vPvB substance.

The mixture does not contain substance(s) included in the list established in accordance with Article 59(1) of REACH for having endocrine disrupting properties, or is not identified as having endocrine disrupting properties in accordance with the criteria set out in Commission Delegated Regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605

**SECTION 3: Composition/information on ingredients****3.2. Mixtures****Chemical characterization**

Aqueous preparation with additives.

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**Myxal HDS**

Revision date: 30.11.2022

Product code: 00320-0220-GHS

Page 2 of 9

**Hazardous components**

CAS No	Chemical name			Quantity
	EC No	Index No	REACH No	
	GHS Classification			
68424-85-1	Quaternary ammonium compounds, benzyl-C12-16-alkyldimethyl, chlorides			< 1 %
	270-325-2		01-2119965180-41	
	Met. Corr. 1, Acute Tox. 4, Skin Corr. 1B, Eye Dam. 1, Aquatic Acute 1, Aquatic Chronic 1; H290 H302 H314 H318 H400 H410			
7173-51-5	Didecyldimethylammonium chloride			< 1 %
	230-525-2	612-131-00-6	01-2119945987-15	
	Acute Tox. 3, Skin Corr. 1B, Eye Dam. 1, Aquatic Acute 1, Aquatic Chronic 2; H301 H314 H318 H400 H411			

Full text of H and EUH statements: see section 16.

**Specific Conc. Limits, M-factors and ATE**

CAS No	EC No	Chemical name	Quantity
	Specific Conc. Limits, M-factors and ATE		
68424-85-1	270-325-2	Quaternary ammonium compounds, benzyl-C12-16-alkyldimethyl, chlorides	< 1 %
	oral: LD50 = 795 mg/kg Aquatic Acute 1; H400: M=10 Aquatic Chronic 1; H410: M=1		
7173-51-5	230-525-2	Didecyldimethylammonium chloride	< 1 %
	dermal: LD50 = 3342 mg/kg; oral: LD50 = 238 mg/kg Aquatic Acute 1; H400: M=10		

**SECTION 4: First aid measures****4.1. Description of first aid measures****General information**

Remove contaminated soaked clothing immediately.  
If you feel unwell, seek medical advice.

**After inhalation**

After inhalation of combustion gases or decomposition products in case of fire, move victim into fresh air.  
In the event of symptoms refer for medical treatment.

**After contact with skin**

Wash hands with water as a precaution.  
Consult a doctor if skin irritation persists.

**After contact with eyes**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes.  
Seek medical treatment by eye specialist.

**After ingestion**

Do not provoke vomiting. Consult physician. Attention in case of vomiting - acute danger of suffocating, produced by foaming ingredients. Rinse mouth. Make drink some glasses of water. The decision whether to provoke vomiting is to be taken by a physician.

**4.2. Most important symptoms and effects, both acute and delayed**

Watch out. Beware, hazard of foam aspiration.  
May cause eye or skin irritation with susceptible persons.

**4.3. Indication of any immediate medical attention and special treatment needed**

Treat symptoms.

**SECTION 5: Firefighting measures****5.1. Extinguishing media**

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**Myxal HDS**

Revision date: 30.11.2022

Product code: 00320-0220-GHS

Page 3 of 9

**Suitable extinguishing media**

Product does not burn, fire-extinguishing activities according to surrounding.

**Unsuitable extinguishing media**

Full water jet

**5.2. Special hazards arising from the substance or mixture**

Not known.

**5.3. Advice for firefighters**

Wear self-contained breathing apparatus and protective suit.

**Additional information**

Cool containers at risk with water spray jet.

Fire residues and contaminated firefighting water must be disposed of in accordance with the local regulations.

**SECTION 6: Accidental release measures****6.1. Personal precautions, protective equipment and emergency procedures****General advice**

Ensure adequate ventilation.

Keep away noninvolved persons.

**For non-emergency personnel**

Do not breathe vapours.

Avoid contact with skin, eyes and clothing.

**For emergency responders**

In case of vapour formation use respirator.

Use personal protective clothing.

**6.2. Environmental precautions**

Do not discharge into the drains/surface waters/ground water.

**6.3. Methods and material for containment and cleaning up****For containment**

Prevent spread over a wide area (e.g. by containment or oil barriers).

**For cleaning up**

Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder).

Take up mechanically and collect in suitable container for disposal.

**6.4. Reference to other sections**

Observe protective instructions (see Sections 7 and 8).

Information for disposal see section 13.

**SECTION 7: Handling and storage****7.1. Precautions for safe handling****Advice on safe handling**

Keep container tightly closed.

Avoid contact with skin, eyes and clothing.

**Advice on protection against fire and explosion**

No special protective measures against fire required.

**7.2. Conditions for safe storage, including any incompatibilities****Requirements for storage rooms and vessels**

Keep containers tightly closed in a dry, well-ventilated place.

**Hints on joint storage**

No materials to be especially mentioned.

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**Myxal HDS**

Revision date: 30.11.2022

Product code: 00320-0220-GHS

Page 4 of 9

**Further information on storage conditions**

Keep away from food, drink and animal feeding stuffs.

**7.3. Specific end use(s)**

Hygienic hand washing

**SECTION 8: Exposure controls/personal protection****8.1. Control parameters****Exposure limits (EH40)**

CAS No	Substance	ppm	mg/m <sup>3</sup>	fibres/ml	Category	Origin
57-55-6	Propane-1,2-diol, particulates	-	10		TWA (8 h)	WEL

**Additional advice on limit values**

This product does not contain any substances for which a Workplace Exposure Limit has been set in concentrations above the limits.

**8.2. Exposure controls****Appropriate engineering controls**

Ensure adequate ventilation, especially in confined areas.

**Protective and hygiene measures**

Wash hands before breaks and immediately after handling the product.

When using do not eat, drink or smoke.

Avoid contact with skin, eyes and clothing.

Remove and wash contaminated clothes before re-use.

**Eye/face protection**

Tightly fitting goggles (EN 166).

**Hand protection**

Also suitable are gloves made of:

Polychloropren - CR (0,5 mm): Breakthrough time > 4 h

Nitrile rubber/nitrile latex - NBR (0,35 mm): Breakthrough time > 4 h

Butyl rubber - Butyl (0,5 mm): Breakthrough time > 8 h

Fluoro-rubber - FKM (0,4 mm): Breakthrough time > 8 h

Polyvinyl chloride - PVC (0,5 mm): Breakthrough time > 4 h

This recommendation refers exclusively to the chemical compatibility and the lab test conforming to EN 374 carried out under lab conditions.

Requirements can vary as a function of the use. Therefore it is necessary to adhere additionally to the recommendations given by the manufacturer of protective gloves.

**Skin protection**

Long sleeved clothing (DIN EN ISO 6530)

**Respiratory protection**

In case of insufficient ventilation wear suitable respiratory equipment (gas filter type A) (EN 14387).

**SECTION 9: Physical and chemical properties****9.1. Information on basic physical and chemical properties**

Physical state:	Liquid
Colour:	Colourless
Odour:	Characteristic

pH-Value (at 20 °C):

**Test method**  
6 (Concentrate)

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**Myxal HDS**

Revision date: 30.11.2022

Product code: 00320-0220-GHS

Page 5 of 9

**Changes in the physical state**

Melting point/freezing point:	n.d.
Boiling point or initial boiling point and boiling range:	n.d.
Sublimation point:	n.a.
Softening point:	n.d.
Flash point:	n.a.
Sustaining combustion:	Not sustaining combustion

**Flammability**

Solid/liquid:	n.a.
Gas:	n.a.

**Explosive properties**

The product is not explosive.

Lower explosion limits:	n.a.
Upper explosion limits:	n.a.
Auto-ignition temperature:	n.a.

**Self-ignition temperature**

Solid:	n.a.
Gas:	n.a.

Decomposition temperature:	n.d.
----------------------------	------

**Oxidizing properties**

Not oxidising.

Vapour pressure:	n.d.
------------------	------

Density (at 20 °C):	0,999 g/cm <sup>3</sup>
---------------------	-------------------------

Bulk density:	n.a.
---------------	------

Water solubility: (at 20 °C)	Miscible
---------------------------------	----------

**Solubility in other solvents**

n.d.

Partition coefficient n-octanol/water:	n.d.
--	------

Viscosity / dynamic:	n.d.
----------------------	------

Viscosity / kinematic:	n.d.
------------------------	------

Flow time:	n.d.
------------	------

Relative vapour density:	n.d.
--------------------------	------

Evaporation rate:	n.d.
-------------------	------

Solvent separation test:	0 %
--------------------------	-----

Solvent content:	0 %
------------------	-----

**9.2. Other information**

No data available

**SECTION 10: Stability and reactivity****10.1. Reactivity**

No decomposition if stored and applied as directed.

**10.2. Chemical stability**

Stable under normal conditions.

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**Myxal HDS**

Revision date: 30.11.2022

Product code: 00320-0220-GHS

Page 6 of 9

**10.3. Possibility of hazardous reactions**

No hazardous reactions known.

**10.4. Conditions to avoid**

To avoid thermal decomposition, do not overheat.

**10.5. Incompatible materials**

No materials to be especially mentioned.

**10.6. Hazardous decomposition products**

No known hazardous decomposition products.

**SECTION 11: Toxicological information****11.1. Information on hazard classes as defined in Regulation (EC) No. 1272/2008****Acute toxicity**Based on available data, the classification criteria are not met.  
No toxicological data available.**Irritation and corrosivity**

Based on available data, the classification criteria are not met.

**Sensitising effects**

Based on available data, the classification criteria are not met.

**Carcinogenic/mutagenic/toxic effects for reproduction**

Based on available data, the classification criteria are not met.

**STOT-single exposure**

Based on available data, the classification criteria are not met.

**STOT-repeated exposure**

Based on available data, the classification criteria are not met.

**Aspiration hazard**

Based on available data, the classification criteria are not met.

**Additional information on tests**

Classification in compliance with the assessment procedure specified in the Regulation (EC) no 1272/2008.

**11.2. Information on other hazards****Endocrine disrupting properties**

No data available

**Other information**Watch out. Beware, hazard of foam aspiration.  
May cause eye or skin irritation with susceptible persons.**SECTION 12: Ecological information****12.1. Toxicity**Ecological data are not available.  
Harmful to aquatic life with long lasting effects.Quaternary ammonium compounds, benzyl-C12-16-alkyldimethyl, chlorides  
LC50/Oncorhynchus mykiss/96 h = 0,085 mg/l  
ErC50/Selenastrum capricornutum/72 h = 0,025 mg/l  
EC50/Daphnia/48 h = 0,016 mg/l  
NOEC/Daphnia/21 d = 0,025 mg/lDidecyldimethylammonium chloride  
LC50/Pimephales promelas/96 h = 0,19 mg/l  
ErC50/Pseudokirchneriella subcapitata/72 h = 0,026 mg/l

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**Myxal HDS**

Revision date: 30.11.2022

Product code: 00320-0220-GHS

Page 7 of 9

EC50/Daphnia magna/48 h = 0,062 mg/l

NOEC/@1203020420./21 d = 0,01 mg/l

NOEC/Danio rerio/34 d = 0,032 mg/l

**12.2. Persistence and degradability**

The surfactant(s) contained in this preparation complies(comply) with the biodegradability criteria as laid down in Regulation (EC) No.648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them, at their direct request or at the request of a detergent manufacturer.

**12.3. Bioaccumulative potential**

No data available

**12.4. Mobility in soil**

No data available

**12.5. Results of PBT and vPvB assessment**

The substances in the mixture do not meet the PBT/vPvB criteria according to UK REACH.

**12.6. Endocrine disrupting properties**

This product does not contain a substance that has endocrine disrupting properties with respect to non-target organisms as no components meets the criteria.

**12.7. Other adverse effects**

Hazardous water pollutant.

**Further information**

This concentrate is not allowed to be released into the sewerage, surface water or groundwater.

**SECTION 13: Disposal considerations****13.1. Waste treatment methods****Disposal recommendations**

Where possible recycling is preferred to disposal.

Can be incinerated, when in compliance with local regulations.

**List of Wastes Code - residues/unused products**

070699 WASTES FROM ORGANIC CHEMICAL PROCESSES; wastes from the MFSU of fats, grease, soaps, detergents, disinfectants and cosmetics; wastes not otherwise specified

**Contaminated packaging**

Empty containers should be taken for local recycling, recovery or waste disposal.

Contaminated packaging should be emptied as far as possible and after appropriate cleansing may be taken for reuse.

Packaging that cannot be cleaned should be disposed of like the product.

**SECTION 14: Transport information****Land transport (ADR/RID)****14.1. UN number:**

No dangerous good in sense of this transport regulation.

**14.2. UN proper shipping name:**

No dangerous good in sense of this transport regulation.

**14.3. Transport hazard class(es):**

No dangerous good in sense of this transport regulation.

**14.4. Packing group:**

No dangerous good in sense of this transport regulation.

**Inland waterways transport (ADN)****14.1. UN number:**

No dangerous good in sense of this transport regulation.

**14.2. UN proper shipping name:**

No dangerous good in sense of this transport regulation.

**14.3. Transport hazard class(es):**

No dangerous good in sense of this transport regulation.

**14.4. Packing group:**

No dangerous good in sense of this transport regulation.

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**Myxal HDS**

Revision date: 30.11.2022

Product code: 00320-0220-GHS

Page 8 of 9

**Marine transport (IMDG)**

- 14.1. UN number:** No dangerous good in sense of this transport regulation.  
**14.2. UN proper shipping name:** No dangerous good in sense of this transport regulation.  
**14.3. Transport hazard class(es):** No dangerous good in sense of this transport regulation.  
**14.4. Packing group:** No dangerous good in sense of this transport regulation.

**Air transport (ICAO-TI/IATA-DGR)**

- 14.1. UN number:** No dangerous good in sense of this transport regulation.  
**14.2. UN proper shipping name:** No dangerous good in sense of this transport regulation.  
**14.3. Transport hazard class(es):** No dangerous good in sense of this transport regulation.  
**14.4. Packing group:** No dangerous good in sense of this transport regulation.

**14.5. Environmental hazards**

ENVIRONMENTALLY HAZARDOUS: No

**14.6. Special precautions for user**

No dangerous good in sense of this transport regulation.

**14.7. Maritime transport in bulk according to IMO instruments**

No dangerous good in sense of this transport regulation.

**SECTION 15: Regulatory information****15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****EU regulatory information**

Restrictions on use (REACH, annex XVII):

Entry 3, Entry 75

2004/42/EC (VOC): 0 %

Information according to 2012/18/EU (SEVESO III): Not subject to 2012/18/EU (SEVESO III)

**National regulatory information**

Employment restrictions:

Observe restrictions to employment for juveniles according to the 'juvenile work protection guideline' (94/33/EC). Observe employment restrictions under the Maternity Protection Directive (92/85/EEC) for expectant or nursing mothers.

**15.2. Chemical safety assessment**

For this substance a chemical safety assessment has not been carried out.

**SECTION 16: Other information****Changes**

Changes in section: 2, 6, 7, 9, 11, 12, 15, 16

**Abbreviations and acronyms**

ADR = Accord européen relatif au transport international des marchandises Dangereuses par Route

RID = Règlement concernant le transport international ferroviaire de marchandises dangereuses

ADN = Accord européen relatif au transport international des marchandises dangereuses par voie de navigation intérieure

IMDG = International Maritime Code for Dangerous Goods

IATA/ICAO = International Air Transport Association / International Civil Aviation Organization

MARPOL = International Convention for the Prevention of Pollution from Ships

IBC-Code = International Code for the Construction and Equipment of Ships Carrying Dangerous Chemicals in Bulk



**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**Myxal HDS**

Revision date: 30.11.2022

Product code: 00320-0220-GHS

Page 9 of 9

GHS = Globally Harmonized System of Classification and Labelling of Chemicals

REACH = Registration, Evaluation, Authorization and Restriction of Chemicals

CAS = Chemical Abstract Service

EN = European norm

ISO = International Organization for Standardization

DIN = Deutsche Industrie Norm

PBT = Persistent Bioaccumulative and Toxic

vPvB = Very Persistent and very Bio-accumulative

LD = Lethal dose

LC = Lethal concentration

EC = Effect concentration

IC = Median immobilisation concentration or median inhibitory concentration

**Relevant H and EUH statements (number and full text)**

H290	May be corrosive to metals.
H301	Toxic if swallowed.
H302	Harmful if swallowed.
H314	Causes severe skin burns and eye damage.
H318	Causes serious eye damage.
H400	Very toxic to aquatic life.
H410	Very toxic to aquatic life with long lasting effects.
H411	Toxic to aquatic life with long lasting effects.
H412	Harmful to aquatic life with long lasting effects.

**Further Information**

Data of items 4 to 8, as well as 10 to 12, do partly not refer to the use and the regular employing of the product (in this sense consult information on use and on product), but to liberation of major amounts in case of accidents and irregularities.

The information describes exclusively the safety requirements for the product(s) and is based on the present level of our knowledge.

The delivery specifications are contained in the corresponding product sheet.

This data does not constitute a guarantee for the characteristics of the product(s) as defined by the legal warranty regulations.

The provision of the safety data sheet does not automatically guarantee the marketability of the product.

(n.a. = not applicable; n.d. = not determined)

*(The data for the hazardous ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)*