

## Product information

# 77 32 115 ESD

## Electronics Diagonal Cutter ESD

DIN ISO 9654 DIN EN 61 340-5



- Pointed head, with small bevel
- Cutting edge hardness approx. 60 HRC
- For fine cutting work, e.g. in electronics and fine mechanics
- Electrically discharging handles - dissipative
- Sturdy, zero-backlash box joint
- Low-friction double spring for gentle and even opening
- The mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Handles with two-colour multi-component grips black/grey
- Ball bearing chrome steel, oil hardened



### General

Article No.	77 32 115 ESD
EAN	4003773025122
Head	mirror polished
Handles	with multi-component grips
Weight	70 g
Dimensions	115 x 67 x 17 mm
Standard	DIN ISO 9654 DIN EN 61 340-5
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details

Cutting capacities medium hard wire (diameter)	Ø 1.0 mm
Cutting capacities hard wire (diameter)	Ø 0.5 mm
Cutting capacities soft wire (diameter)	Ø 0.3 – 1.3 mm
Jaw length (B)	14 mm
Jaw thickness (joint) (D)	7 mm
Head width (A)	11 mm
ESD	yes

## Technical details



*technical change and errors excepted*