


1	2	3	4	5	6	7	8											
Order-No.	Shell Size / for No. of Contacts	A ±0.3	B ±0.1	C ±0.3	D ±0.3	E ±0.3	∅F min - max	G ±0.3	H ±0.3	J ±0.3	K ±0.3	L ±0.3	M ±0.5	N ±0.3	Q ±0.3	R ±0.3	T ±0.3	U
FKH1-A	1 / 9	10	25	31.2	31.8	16	4.5 - 7	20	35	11.5	17	19.6	16.5	12	7.3	15	13	9.6
FKH2-A	2 / 15	16.1	33.3	40	32	16	4.5 - 7	21.8	34.7	11.4	25.5	27.8	16	12	12.8	13	13	9.2
FKH3-A	3 / 25	27.8	47	53.7	35	16	8 - 10.5	32	37.7	11.4	39	41.6	20	18	25.6	14	13	9.2
FKH4-A	4 / 37	44.4	63.5	70.1	41	16	8 - 10.5	50	43.7	11.5	55.6	58	26	18	45.3	19.1	-	9.3
FKH5-A	5 / 50	42	61.1	67.8	41	18.5	10.5 - 12	48	43.7	14	53.4	55.7	26	18	42.4	19.1	-	9.2

∅F = Cable diameter

view of the hoods without lid



No.	St.	Part	Type Description/Material
4	2	Cable clamp screw	Steel
3	1	Cable clamp	Steel
2	2	Shell screw	Steel
1	1	Hood	FKH1-5A / Polyester
Surface plating/Colour/Class			
zinc plated			
tin plated			
zinc plated			
nickel plated			

Measurement without tolerance acc. to ISO 2768-m		SCALE	TITLE
NAME / DATE	Anke Meyer-Richter	2.1	Plastic Hood
CHECKED	Anke Meyer-Richter		
DATE	07-01-2013	CH.-NO.	DWG.NO.
REV.	04-09-2008	22231	FKH1-5A
REV.			REPLACEMENT FOR: FKH1-5A_d.ACAD
			PAGES 1

① max. torque are 40 Ncm
Hood is snapped together
Part-No. 2, 3 and 4 not mounted

COMMENT: ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT, IT MAY NOT BE REPRODUCED NOR MADE AVAILABLE TO A THIRD PARTY. AND IT ALSO MAY NOT BE IMPROPERLY USED BY THE RECEIVER, OR A THIRD PARTY.