SPEC


Spec No.	TQ3C-8EAF0-E1YAA26-00
Date	June 10, 2011

#### TYPE: TCG070WVLPAAGA-AC00

< 7.0 inch WVGA transmissive color TFT
with LED backlight / with touch panel. >

#### CONTENTS

- 1. Application
- 2. Construction and outline
- 3. Mechanical specifications
- 4. Absolute maximum ratings
- 5. Electrical characteristics
- 6. Optical characteristics
- 7. Interface signals
- 8. Input timing characteristics
- 9. Backlight characteristics
- 10. Design guidance for analog touch panel
- 11. Lot number identification
- 12. Warranty
- 13. Precautions for use
- 14. Reliability test data
- 15. Outline drawing



KYOCERA CORPORATION KAGOSHIMA HAYATO PLANT LCD DIVISION

This specification is subject to change without notice. Consult Kyocera before ordering.

I	Original	Designed by: 1	Engineering dep	ot.	Confirmed by: QA dept.		
L	Issue Date	Prepared	Checked	Approved	Checked	Approved	
	June 10, 2011	S.Hatanaka	y. Ikeda	M.Fyitani	1-Hamas	To Suf	

Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAA26-00	TCG070WVLPAAGA-AC00	-

### Warning

- 1. This Kyocera LCD module has been specifically designed for use only in electronic devices and industrial machines in the area of audio control, office automation, industrial control, home appliances, etc. The module should not be used in applications where the highest level of safety and reliability are required and module failure or malfunction of such module results in physical harm or loss of life, as well as enormous damage or loss. Such fields of applications include, without limitation, medical, aerospace, communications infrastructure, atomic energy control. Kyocera expressly disclaims any and all liability resulting in any way to the use of the module in such applications.
- 2. Customer agrees to indemnify, defend and hold Kyocera harmless from and against any and all actions, claims, damages, liabilities, awards, costs, and expenses, including legal expenses, resulting from or arising out of Customer's use, or sale for use, or Kyocera modules in applications.

### Caution

1. Kyocera shall have the right, which Customer hereby acknowledges, to immediately scrap or destroy tooling for Kyocera modules for which no Purchase Orders have been received from the Customer in a two-year period.



Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAA26-00	TCG070WVLPAAGA-AC00	-

## Revision record

	Date	Design	ed by:	Engineering of	lept.	Confirmed by	: QA dept.
	Date	Prepared		Checked	Approved	Checked	Approved
D 11	D :	D			T		
Rev.No.	Date	Page			Description	ons	



Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAA26-00	TCG070WVLPAAGA-AC00	1

### 1. Application

This document defines the specification of TCG070WVLPAAGA-AC00. (RoHS Compliant)

#### 2. Construction and outline

LCD : Transmissive color dot matrix type TFT

Backlight system : LED

Polarizer : Anti-Glare treatment

Additional circuit : Timing controller, Power supply (3.3V input)

(without constant current circuit for LED Backlight)

Touch panel : Analog type, (Glass / Glass)
Surface film : Glare Anti-finger print treatment

### 3. Mechanical specifications

#### 3-1. LCD

Item	Specification	Unit
Outline dimensions 1)	165(W)×(104.4)(H)×10.04(D)	mm
Active area	152.4(W)×91.44(H) (17.8cm/7.0 inch(Diagonal))	mm
Dot format	800×(R,G,B)(W)×480(H)	dot
Dot pitch	0.0635(W)×0.1905(H)	mm
Base color 2)	Normally White	-
Mass	250	g

- 1) Projection not included. Please refer to outline for details.
- 2) Due to the characteristics of the LCD material, the color varies with environmental temperature.

### 3-2. Touch panel

Item			Specification	Unit
Input			Radius-0.8 stylus or Finger	-
Astrodise Face	Before reliability test		0.1 ~ 2.0	N
Actuation Force	After reliability test	1)	0.1 ~ 3.0	N
On anotin a life	Striking(Finger-input)	2)	1 million	hits
Operating life	Sliding(Stylus-input)	3)	100 thousand	characters
Transmittance			Typ.80(at full wavelength)	%
Surface hardness		3H or more(Pencil hardness)	-	
Static load		4)	Min.5	kgf



 Spec No.
 Part No.
 Page

 TQ3C-8EAF0-E1YAA26-00
 TCG070WVLPAAGA-AC00
 2

1) Pleas refer to "14.reliability test data" for details (The tested panel is not used in any other tests)

#### 2) Striking test condition

Testing rod : Silicon rubber (Hardness: $60^{\circ}$ ), Tip : R = 6.0,

Testing location : Center of active area

Load : 2.45N Cycle : 2hits/sec

Judgment : No defect in function

: No appearance defect which causes trouble to use. \*Dents, blurs and marks on surface film: neglected

#### 3) Sliding test condition

Testing rod : Polyacetal resin, Tip : R = 0.8

Testing location : Center of active area

Load : 2.45N
Input length : 10mm
Input speed : 50mm/sec

Sliding times : 10mm sliding (back and forth) counts as 2 times.

Judgment : No defect in function

: No appearance defect which causes trouble to use.
\*Dents, blurs and marks on surface film: neglected

#### 4) Static load test condition

Testing rod : Silicon rubber, Tip: 10, Hardness:50°

Input period : 2sec

Pressure location : 30mm from edge (shorter edge)

Setting method : Retain of the touch panel with 1mm clearance

Judgement : No glass cracking

Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAA26-00	TCG070WVLPAAGA-AC00	3

#### 4. Absolute maximum ratings

#### 4-1. Electrical absolute maximum ratings

Item		Symbol	Min.	Max.	Unit
Supply voltage		$V_{\mathrm{DD}}$	-0.3	4.5	V
Input signal voltage	1)	$V_{\rm IN}$	-0.3	4.5	V
LED forward current	2) 3)	IF	-	100	mA
Supply voltage for touch panel		$V_{\mathrm{TP}}$	0	6.0	V
Input current of touch panel		${ m I}_{ m TP}$	0	0.5	mA

- 1) Input signal: CK, R0 ~ R5, G0 ~ G5, B0 ~ B5, H<sub>SYNC</sub>, V<sub>SYNC</sub>, ENAB, CM, SC
- 2) For each "AN-CA"
- 3) Do not apply reversed voltage.

#### 4-2. Environmental absolute maximum ratings

Item		Symbol	Min.	Max.	Unit
Operating temperature	1)	Тор	-20	70	$^{\circ}\mathrm{C}$
Storage temperature	2)	$T_{STO}$	-30	80	$^{\circ}\mathrm{C}$
Operating humidity	3)	Нор	10	4)	%RH
Storage humidity	3)	Нѕто	10	4)	%RH
Vibration		-	5)	5)	-
Shock		-	6)	6)	-

- 1) Operating temperature means a temperature which operation shall be guaranteed. Since display performance is evaluated at 25°C, another temperature range should be confirmed.
- 2) Temp. = -30°C < 48h, Temp. = 80°C < 168h Store LCD at normal temperature/humidity. Keep them free from vibration and shock. An LCD that is kept at a low or a high temperature for a long time can be defective due to other conditions, even if the low or high temperature satisfies the standard. (Please refer to "Precautions for Use" for details.)
- 3) Non-condensing
- 4) Temp. 40°C, 85%RH Max. Temp. > 40°C, Absolute humidity shall be less than 85%RH at 40°C.

5)

Frequency	10 ~ 55 Hz	Acceleration value
Vibration width	0.15mm	$(0.3 \sim 9 \text{ m/s}^2)$
Interval	10-55-10	Hz 1 minutes

2 hours in each direction X, Y, Z (6 hours total)

EIAJ ED-2531

6) Acceleration: 490 m/s<sup>2</sup>, Pulse width: 11 ms 3 times in each direction:  $\pm X$ ,  $\pm Y$ ,  $\pm Z$ 

EIAJ ED-2531



Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAA26-00	TCG070WVLPAAGA-AC00	4


## 5. Electrical characteristics

#### 5-1. LCD

Temp. =  $-20 \sim 70$ °C

Item		Symbol	Condition	Min.	Typ.	Max.	Unit
Supply voltage	1)	$V_{ m DD}$	-	3.0	3.3	3.6	V
Current consumption		${ m I}_{ m DD}$	2)	-	(180)	(235)	mA
Permissive input ripple voltage		$V_{\mathrm{RP}}$	-	-	-	100	mVp-p
	3)	$ m V_{IL}$	"Low" level	0	-	0.8	V
I a seek of more level to me		$V_{\mathrm{IH}}$	"High" level	2.5	-	$ m V_{DD}$	V
Input signal voltage		$V_{\mathrm{IL}}$	"Low" level	0	-	$0.3~\mathrm{V_{DD}}$	V
	4)	V <sub>IH</sub>	"High" level	0.7 V <sub>DD</sub>	-	$V_{\mathrm{DD}}$	V

### 1) $V_{DD}$ -turn-on conditions



### 2) Display pattern:

$$V_{DD} = 3.3V$$
, Temp. = 25°C

- 3) Input signal: CK, R0 ~ R5, G0 ~ G5, B0 ~ B5, H<sub>SYNC</sub>, V<sub>SYNC</sub>, ENAB, CM
- 4) Input signal: SC




Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAA26-00	TCG070WVLPAAGA-AC00	5


### 5-2. Touch panel

Item	Symbol	Condition	Min.	Тур.	Max.	Unit
Supply voltage for touch panel	$V_{\mathrm{TP}}$	-	-	5.0	-	V
m	xL-xR	-	200	-	2,000	Ω
Terminal resistance 1)	yU-yL	-	100	-	700	Ω
Linearity 2)	-	-	less than ±2.5		2.5	%
Insulation resistance 3)	-	DC25V	50	-	-	$M\Omega$
Chattering 4)	-	at ON/OFF	10	ess than 1	0	ms

- 1) Resistance between terminal xL and xR, or between yU and yL
- 2) Apply 5VDC to the terminal xL-xR, and measure the output voltage at terminal y when a random input is applied in the active area. Measure the difference between the output and theoretical voltages. (Measure the actual voltage at the terminal using the same method.)



- 3) Resistance between the upper and lower terminals.
- 4) Apply 5VDC to the terminal xL-xR, and measure the oscillation at terminal y when applying a random input in the active area. (Measure the oscillation at terminal x using the same method.)



Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAA26-00	TCG070WVLPAAGA-AC00	6

## 6. Optical characteristics


Measuring spot = 6.0mm, Temp. = 25°C

					0 1		•	
Item		Symbol	Condition	Min.	Тур.	Max.	Unit	
Posnonso timo	Rise	τг	= =0°	-	5	-	ms	
Response time	Down	τd	= =0°	-	25	1	ms	
T7: 1		UPPER		-	60	-	1	
Viewing angle View direction	range	LOWER	CR 10	-	80	-	deg.	
: 12 o'clo (Gray in		LEFT	CK 10	-	80	-	d o or	
(Gray III	version)	$\phi$ right		-	80	-	deg.	
Contrast ratio		$\operatorname{CR}$	= =0°	700	1000	•	1	
Brightness		L	IF=60mA/Line	200	280	-	cd/m²	
Luminance(Br	ightness)	LU	-	70	-	-	%	
	Red	X	= =0° = =0°	0.550	0.600	0.650		
		У		0.300	0.350	0.400		
		X		0.270	0.320	0.370		
Chromaticity	Green	У	0	0.500	0.550	0.600		
coordinates	Dl	X	= =0°	0.100	0.150	0.200	-	
	Blue	у	0	0.070	0.120	0.170		
	XX71 :4	X	00	0.240	0.290	0.340		
	White	У	= =0°	0.255	0.305	0.355		

### 6-1. Definition of contrast ratio

CR(Contrast ratio) = Brightness with all pixels "White"
Brightness with all pixels "Black"


### 6-2. Definition of response time






Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAA26-00	TCG070WVLPAAGA-AC00	7

## 6-3. Definition of viewing angle



### 6-4. Brightness measuring points



- 1) Rating is defined as the white brightness at center of display screen(3).
- 2) The brightness uniformity is calculated by using following formula.

Brightness uniformity = 
$$\frac{\text{Minimum brightness from 1 to 5}}{\text{Maximum brightness from 1 to 5}} \times 100 [\%]$$

3) 30 minutes after LED is turned on. (Ambient Temp.=25  $\,$  )



Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAA26-00	TCG070WVLPAAGA-AC00	8

# 7. Interface signals

### 7-1. LCD

L. LCD	~		
No.	Symbol	Description	Level
1	AN1	Anode1	
2	AN2	Anode2	
3	CA1	Cathode1	
4	CA2	Cathode2	
5	$V_{ m DD}$	3.3V power supply	
6	$V_{ m DD}$	3.3V power supply	
7	CM	Mode select signal (High or Open: Necessity of V• H <sub>SYNC</sub> , GND: Uunecessity of V• H <sub>SYNC</sub> )	
8	ENAB	Data Enable (positive)	
9	$V_{\mathrm{SYNC}}$	Vertical synchronous signal (negative)(fix low or high: when CM fixed to GND)	
10	Hsync	Horizontal synchronous signal (negative) (fix low or high: when CM fixed to GND)	
11	GND	GND	
12	B5	BLUE data signal (MSB)	
13	B4	BLUE data signal	
14	В3	BLUE data signal	
15	GND	GND	
16	B2	BLUE data signal	
17	B1	BLUE data signal	
18	В0	BLUE data signal (LSB)	
19	GND	GND	
20	G5	GREEN data signal (MSB)	
21	G4	GREEN data signal	
22	G3	GREEN data signal	
23	GND	GND	
24	G2	GREEN data signal	
25	G1	GREEN data signal	
26	G0	GREEN data signal (LSB)	
27	GND	GND	
28	R5	RED data signal (MSB)	
29	R4	RED data signal	
30	R3	RED data signal	
31	GND	GND	
32	R2	RED data signal	
33	R1	RED data signal	
34	R0	RED data signal (LSB)	
35	SC	Scan direction control(GND or Open: Normal、High: Reverse)	
36	GND	GND	
37	GND	GND	
38	CK	Sampling clock	
39	GND	GND	
40	GND	GND	

LCD connector : IMSA-9681S-40A-GF (IRISO)

Recommended matching FFC or FPC : 0.5mm pitch



Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAA26-00	TCG070WVLPAAGA-AC00	9

### 1) Scanning

SC: GND or Open SC: High





## 7-2. Touch panel

No.	Symbol	Description
1	xR	x-Right terminal
2	уL	y-Lower terminal
3	xL	x-Left terminal
4	уU	y-Upper terminal

Touch panel side connector : 1mm pitch

Recommended matching connector : Series 9616 (IRISO)

: Series 9610 (IRISO): Series FMS (JST)



Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAA26-00	TCG070WVLPAAGA-AC00	10

## 8. Input timing characteristics

8-1. CM: High or Open (Necessity of V·HSYNC)

#### 8-1-1. Timing characteristics


	Item	Symbol	Min.	Тур.	Max.	Unit	Note
	Frequency	Fck	29.88	33.2	36.52	MHz	
Cl. 1	Period	Тс	27.4	30.1	33.5	ns	
Clock	High time	Tch	12	-	-	ns	
	Low time	Tel	12	-	-	ns	
D. 4	Set up time	Tds	5	-	-	ns	
Data	Hold time	Tdh	10	-	-	ns	
D ( F 11	Set up time	Tes	5	-	-	ns	
Data Enable	Hold time	Teh	10	-	-	ns	
	Set up time	Ths	5	-	-	ns	
	Hold time	Thh	10	-	-	ns	
	Period	Th	944	1056	1088	Тс	
Horizontal sync. signal			-	31.8	-	μs	
Signai	Pulse width	Thp	4	128	-	Тс	
	Front porch	Thf	-	40	-	Тс	
	Back porch	Thb	7	88	-	Тс	
Horizontal display	period	Thd	800			Тс	
	D : 1	TD.	516	525	534	Th	
	Period	Tv	14.7	16.6	17.4	ms	
Vertical sync. signal	Pulse width	Tvp	1	2	-	Th	
signai	Front porch	Tvf	-	11	-	Th	
	Back porch	Tvb	4	32	-	Th	
Vertical display per	riod	Tvd		480		Th	

- 1) In case of lower frequency, the deterioration of the display quality, flicker etc., may occur.
- 2) If CK is fixed to "H" or "L" level for certain period while ENAB is supplied, the panel may be damaged.
- 3) When dimming LED by PWM, please adjust LCD operating signal timing and LED driving frequency, to optimize the display quality. There is a possibility that flicker is observed by the interference of LCD operating signal timing and LED driving condition (especially driving frequency), even if the condition satisfies above timing specification.
- 4) Do not make Tv, Th, and Thp fluctuate.
- 5) CK count of each Horizontal Scanning Time should be always the same. Vertical invalid data period should be "n" X "Horizontal Scanning Time" . (n: integer) Frame period should be always the same.



Spec No.Part No.PageTQ3C-8EAF0-E1YAA26-00TCG070WVLPAAGA-AC0011

### 8-1-2. Input timing characteristics





Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAA26-00	TCG070WVLPAAGA-AC00	12

### 8-2 . CM : GND ( Uunecessity of V $\!\!^{\bullet}\!\!$ Hsync )

#### 8-2-1. Timing characteristics


	Item	Symbol	Min.	Тур.	Max.	Unit	Note
	Frequency	Fck	29.88	33.2	36.52	MHz	
	Period	Тс	27.4	30.1	33.5	ns	
Clock	High time	Tch	12	-	-	ns	
	Low time	Tcl	12	-	-	ns	
Data	Set up time	Tds	5	-	-	ns	
Data	Hold time	Tdh	10	-	-	ns	
	Set up time	Tes	5	-	-	ns	
	Hold time	Teh	10	-	-	ns	
	Period	m)	1024	1056	1088	Тс	
Enable	Period	Th	-	31.8	-	μs	
Enable	Horizontal display period	Thd		800		Тс	
	Davied	Tv	487	525	550	Th	
	Period	1 V	14.7	16.6	17.4	ms	
	Vertical display period	Tvd		480		Th	

- 1) In case of lower frequency, the deterioration of the display quality, flicker etc., may occur.
- 2) If CK is fixed to "H" or "L" level for certain period while ENAB is supplied, the panel may be damaged.
- 3) When dimming LED by PWM, please adjust LCD operating signal timing and LED driving frequency, to optimize the display quality. There is a possibility that flicker is observed by the interference of LCD operating signal timing and LED driving condition (especially driving frequency), even if the condition satisfies above timing specification.
- 4) Do not make Tv, Th, and Thp fluctuate.
- 5) CK count of each Horizontal Scanning Time should be always the same. Vertical invalid data period should be "n" X "Horizontal Scanning Time" . (n: integer) Frame period should be always the same.




Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAA26-00	TCG070WVLPAAGA-AC00	13

### 8-2-2. Input timing characteristics



### 8-3. Input Data Signals and Display position on the screen





Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAA26-00	TCG070WVLPAAGA-AC00	14

#### 9. Backlight characteristics

Item		Symbol	Min.	Тур.	Max.	Unit	Note
Forward current	1)	IF	1	60	-	mA	Ta=-20 ~ 70°C
	1)	VF	1	12.6	14.7	V	IF=60mA, Ta=-20
Forward voltage			1	12.0	14.1	V	IF=60mA, Ta=25
			-	11.6	13.8	V	IF=60mA, Ta=70
Operating life time	2), 3)	Т	-	70,000	-	h	IF=60mA, Ta=25

- 1) For each "AN-CA"
- 2) When brightness decrease 50% of minimum brightness.

  The average life of a LED will decrease when the LCD is operating at higher temperatures.
- 3) Life time is estimated data. (Condition: IF=60mA, Ta=25 in chamber).
- 4) An input current below (15)mA may reduce the brightness uniformity of the LED backlight. This is because the amount of light from each LED chip is different. Therefore, please evaluate carefully before finalizing the input current.

#### 10. Design guidance for analog touch panel

10-1. Electrical (In customer's design, please remember the following considerations.)

- 1) Do not use the current regulated circuit.
- 2) Keep the current limit with top and bottom layer. (Please refer to "Electrical absolute maximum ratings" for details.)
- 3) Analog touch panel can not sense two points touching separately.
- 4) A contact resistance is appeared at the touch point between top and bottom layer. After this resistance has stable read of the touch panel position data.
- 5) Because noise of inverter or peripheral circuits may interfere signal of touch panel itself it is necessary to design carefully in advance to avoid these noise problem.

#### 10-2. Software

- 1) Do the "User Calibration".
- 2) "User Calibration" may be needed with long term using. Include "User Calibration" menu in your software.
- 3) When drawing a line with a stylus, there may be a slight discontinuity when the stylus passes over a spacer-dot. If necessary, please provide a compensation feature within your software.

#### 10-3. Mounting on display and housing bezel

- 1) Do not use an adhesive tape to bond it on the front of touch panel and hang it to the housing bezel.
- 2) This touch panel has an airtight but not watertight structure. Please not to use it for the applications requiring watertight or under the environments occurred condensation. If it is expected to be exposed to the environments that vapor, moisture or other liquids may seep inside a bezel, please be sure to take some measurements for drip-proof or waterproof by using sealing materials on the bezel.
- 3) Please mount the touch panel so that it does not move or slide relative to the LCD, even when vibration or shock is applied and even when high humidity or high temperature may weaken the mounting adhesive.



Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAA26-00	TCG070WVLPAAGA-AC00	15

#### 11. Lot number identification

The lot number shall be indicated on the back of the backlight case of each LCD.

No1. - No5. above indicate

- 1. Year code
- 2. Month code
- 3. Date
- 4. Version Number
- 5. Country of origin (Japan or China)

Year	2011	2012	2013	2014	2015	2016
Code	1	2	3	4	5	6

Ī	Month	Jan.	Feb.	Mar.	Apr.	May	Jun.
	Code	1	2	3	4	5	6

Month	Jul.	Aug.	Sep.	Oct.	Nov.	Dec.
Code	7	8	9	X	Y	Z

#### 12. Warranty

## 12-1. Incoming inspection

Please inspect the LCD within one month after your receipt.

#### 12-2. Production warranty

Kyocera warrants its LCD's for a period of 12 months from the ship date. Kyocera shall, by mutual agreement, replace or re-work defective LCD's that are shown to be Kyocera's responsibility.



Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAA26-00	TCG070WVLPAAGA-AC00	16

#### 13. Precautions for use

#### 13-1. Installation of the LCD

- 1) The LCD shall be installed so that there is no pressure on the LSI chips.
- 2) The LCD shall be installed flat, without twisting or bending.
- 3) Must maintain a gap between inside of bezel and touch panel to avoid malfunction or electrode damage of touch panel.
- 4) A transparent protection sheet is attached to the touch panel. Please remove the protection film slowly before use, paying attention to static electricity.

#### 13-2. Static electricity

- 1) Since CMOS ICs are mounted directly onto the LCD glass, protection from static electricity is required.
- 2) Workers should use body grounding. Operator should wear ground straps.

#### 13-3. LCD operation

1) The LCD shall be operated within the limits specified. Operation at values outside of these limits may shorten life, and/or harm display images.

#### 13-4. Storage

- The LCD shall be stored within the temperature and humidity limits specified.
   Store in a dark area, and protect the LCD from direct sunlight or fluorescent light.
- 2) Always store the LCD so that it is free from external pressure onto it.

#### 13-5. Usage

- 1) <u>DO NOT</u> store in a high humidity environment for extended periods. Polarizer degradation bubbles, and/or peeling off of the polarizer may result.
- 2) Do not push or rub the touch panel's surface with hard to sharp objects such as knives, or the touch panel may be scratched.
- 3) When the touch panel is dirty, gently wipe the surface with a soft cloth, sometimes moistene d by mild detergent or alcohol. If a hazardous chemical is dropped on the touch panel by mi stake, wipe it off right away to prevent human contact.
- 4) The touch panel is made of glass. It may break when dropped, or vibrated excessively. Usually there is a film on the surface of the glass which would prevent broken glass from scattering, but nevertheless handle it carefully during assembly and treat it gently during use.
- 5) Touch panel edges are sharp, so they have a possibility of cutting your body, for example your finger. Handle the touch panel with enough care to prevent cuts. When you hold the touch panel, put on the protector, for example the gloves which have a strength enough to stand sharpness of touch panel edges.
- 6) Always keep the LCD free from condensation during testing. Condensation may permanently spot or stain the polarizer.
- 7) Do not disassemble LCD because it will result in damage.
- 8) This Kyocera LCD has been specifically designed for use in general electronic devices, but not for use in a special environment such as usage in an active gas. Hence, when the LCD is supposed to be used in a special environment, evaluate the LCD thoroughly beforehand and do not expose the LCD to chemicals such as an active gas.



Spec No.	Part No.	Page
TQ3C-8EAF0-E1YAA26-00	TCG070WVLPAAGA-AC00	17

- 9) Please do not use solid-base image pattern for long hours because a temporary afterimage may appear. We recommend using screen saver etc. in cases where a solid-base image pattern must be used.
- 10) Liquid crystal may leak when the LCD is broken. Be careful not to let the fluid go into your eyes and mouth. In the case the fluid touches your body; rinse it off right away with water and soap.


#### 14. Reliability test data


Test item	Test condition	Test time	Judgement		
High temp. atmosphere	$\sim$ 2/10h   Current consumption		Current consumption	: No defect : No defect : No defect	
Low temp. atmosphere	-30°C	240h	Current consumption	: No defect : No defect : No defect	
High temp. humidity atmosphere	High temp. Display quality humidity 40°C 90% RH 240h Current consumption		Current consumption	: No defect : No defect : No defect	
Temp. cycle	-30°C 0.5h R.T. 0.5h 80°C 0.5h	10cycles	Current consumption	: No defect : No defect : No defect	
High temp. operation	operation 70°C 500h Current of		Current consumption :	: No defect : No defect : No defect	
Point Activation 1)	tivation $\begin{array}{c cccc} \text{Tip}: R = 6.0 & \text{one} \\ \text{Hardness } 60^{\circ} & \text{million} \\ \text{Hitting force } 2.45N & \text{times} \\ \text{Hitting speed } 2 \text{ time/s} & \text{No appearance def} \end{array}$			: No defect : No defect ffects touch panel	
Sliding 1)	Polyacetal resin, Tip: R = 0.8 Load 2.45N Input length 10mm Input speed 50mm/s	100 thousand times 3)	usand Actuation Force : No defines		

- 1) Test in center of active area.
- 2) Dents, blurs and marks on surface film: neglected.
- 3) 10mm sliding (back and forth) counts as 2 times.
- 4) Temp. cycle test (Heat shock included): the LCD shall be tested after leaving it stabilize at room temperature for 2 hours after the last cycle.
- 5) An operational test was performed after the following conditions. First, the touch panel was left for a certain time under 5V voltages applied (without touch), Then it was left at room temperature (No VDC applied) for 2 hours.
- 6) Each test item uses a test LCD only once. The tested LCD is not used in any other tests.
- 7) The LCD is tested in circumstances in which there is no condensation.
- 8) The reliability test is not an out-going inspection.
- 9) The result of the reliability test is for your reference purpose only.

  The reliability test is conducted only to examine the LCD's capability.







	Spec No.	TQ3C-8EAF0-E2YAA26-00
Г	Date	June 10, 2011

## KYOCERA INSPECTION STANDARD

TYPE: TCG070WVLPAAGA-AC00

KYOCERA CORPORATION SHIGA YASU PLANT LCD DIVISION

Original	Designed by:	esigned by : Engineering dept.			Confirmed by : QA dept.		
Issue Date	Prepared	Checked	Approved	Checked	Approved		
June 10, 2011	S.Hatanaka	y. Ikeda	M.Fujitani	I Hamars	To Suf		



Spec No.	Part No.	Page
TQ3C-8EAF0-E2YAA26-00	TCG070WVLPAAGA-AC00	-

## Revision record

Date		Designe	ed by:	Engineering dept. Confirmed by EQA dept.			: QA dept.
	Date	Prepa	ıred	Checked	Approved	Checked	Approved
Rev.No.	Date	Page			Description	ons	



Spec No.	Part No.	Page
TQ3C-8EAF0-E2YAA26-00	TCG070WVLPAAGA-AC00	1

## Visuals specification

#### Note

			Note				
General	reviewe consent	reviewed by Kyocera, and an additional standard shall be determined by mutual consent.					
		=	shall not be applicable to outside of the area.				
	3. Inspects Lumina	ion conditions ance	: 500 Lux min.				
	Inspect Temper	ion distance rature	: 300 mm. : 25 ± 5				
	Direction	on	: Directly above				
Definition of	Dot defect	Bright dot defect	The dot is constantly "on" when power applied to the				
inspection item			LCD, even when all "Black" data sent to the screen.				
			Inspection tool: 5% Transparency neutral density filter.				
			Count dot: If the dot is visible through the filter.				
			Don't count dot: If the dot is not visible through the				
			filter.  RGBRGBRGB RGBRGB RGBRGBRGB  dot defect				
		Black dot defect	The dot is constantly "off" when power applied to the LCD, even when all "White" data sent to the screen.				
		Adjacent dot	Adjacent dot defect is defined as two or more bright dot defects or black dot defects.				
			R G B R G B R G B R G B R G B R G B R G B R G B R G B				
	External	Bubble, Scratch,	Visible operating (all pixels "Black" or "White") and non				
	inspection	Foreign particle (Polarizer, Cell, Backlight)	operating.				
		_	December the color of the cons				
		Appearance inspection	Does not satisfy the value at the spec.				
	Others	LED wires	Damaged to the LED wires, connector, pin, functional failure or appearance failure.				
	Definition of size	Definition of	circle size Definition of linear size				
		d = (a + b)/2					



Spec No.	Part No.	Page
TQ3C-8EAF0-E2YAA26-00	TCG070WVLPAAGA-AC00	2

#### 2) Standard

2) Standa		1		Т				
	fication	_	tion item	Judgement standard				
Defect	Dot	Bright dot defect		Acceptable number	: 4			
(in LCD	defect			Bright dot spacing	: 5 mm or more			
glass)		Black dot defect		Acceptable number		: 5		
				Black dot spacing		: 5 mm	or more	
		2 dot join	Bright dot	Acceptable number		: 2		
			defect	Acceptable number		• 4		
			Black dot defect	Acceptable number		: 3		
		3 or more	dots join	Acceptable number		: 0		
		Total dot d	lefects	Acceptable number		: 5 Ma:	X	
	Others	White dot,	Dark dot					
		(Circle)		Size (mn	n)	Ac	ceptable number	
				d	0.2		(Neglected)	
				0.2 < d	0.4		5	
				0.4 < d	0.5		3	
				0.5 < d			0	
External	inspection	Polarizer (	Scratch)					
(Defect or	_		,	Width (mm)	Length (	mm)	Acceptable number	
Polarizer				W 0.1	-	,	(Neglected)	
between I					L	5.0	(Neglected)	
and LCD				0.1 < W 0.3	5.0 < L		0	
	g-0000,			0.3 < W	-		0	
		Polarizer (	Bubble)					
				Size (mn	າ)	Ac	ceptable number	
				d	0.2		(Neglected)	
				0.2 < d	0.3		5	
				0.3 < d	0.5		3	
				0.5 < d			0	
		Foreign pa	ırticle					
		( Circular		Size (mn	n)	Ac	ceptable number	
				d	0.2		(Neglected)	
				0.2 < d	0.4		5	
				0.4 < d	0.5		3	
				0.5 < d	d		0	
		Foreign pa	ırticle					
		(Linear s		Width (mm)	Length	(mm)	Acceptable number	
		Scratch	•	W 0.03			(Neglected)	
					L	2.0	(Neglected)	
				0.03 < W 0.1	2.0 < L	4.0	3	
					4.0 < L		0	
				0.1 < W	-		(According to	
							circular shape)	



Spec No.	Part No.	Page
TQ3C-8EAF0-E2YAA26-00	TCG070WVLPAAGA-AC00	3

Inspection item	Judgement standard						
Scratch,	( W = Width, L = Length, D = Diameter = (major axis + minor axis)/ 2)						
Foreign particle	Item	Width(mm) Length(mm) Acceptable number					
(Touch screen	100111	W	0.03	L	20	1100	Neglected
portion)		0.03 < W	0.05	L	10	2nce	es within φ20mm
	Scratch	0.05 < W	0.08	L	6		es within φ20mm
		0.08 < W	0.1	L	4		es within φ30mm
	Foreign	W	0.05	Negle		Tpc	Neglected
	( line like )	0.05 < W	0.1	L	5	2pce	es within φ30mm
	Foreign		D	0.2		_F -	Neglected
	( circle like )	0.2		0.3		2рс	es within φ30mm
	Above are app	L				-1	Ψ
				ınd dan	nage a	ffecte	d seriously to the
	electrical perfo						
Glass crack							
(Touch screen	Item		Size (n	nm)			Acceptable
portion)							number
			/	z /	X	3	
	Conner	××	$\sqrt{\langle}$		V	3	2 pcs
	crack				Y	3	/panel
					Z	< t	
	Crack in	×>	××		X	5	
	other area				Y	1.5	2 pcs
	than in				1	1.0	/side
	corner	2			Z	< t	
	Progressive crack		$\Rightarrow$	/	/		0 pcs (NG even 1pcs)
Newton's ring	All Newton Ring Border around t					ected.	7 4

