DC Axial Fan 60mm x 60mm x 15mm







Electrical Characteristic

Rated Voltage	24V DC	
Rated Current	75mA / Max. 87mA	
Rated Power Consumption	1.80W / Max. 2.09W	
Safety Power Consumption	2.02W	
Operating Voltage Range	8 to 27.6V DC	
Starting Voltage	8V DC (25°C Power ON/OFF)	
Operating Temperature Range	Range -10°C to +70°C	
Storage Temperature Range	-40°C to +70°C	

Mechanical Characteristics

Motor Design	Single Phase, 4-Pole Bushless DC Motor	
Bearing System	Vapo Bearing	
Power Connection Type	#26AWG - 2 Lead Wires; Red (+), Black (-)	
Frame Material	Thermoplastic PBT of UL 94V-0	
Fan Blade Material	Thermoplastic PBT of UL 94V-0	
Rotation Direction	Counter-Clockwise (Viewed from Front of Fan Blade)	
Mounting Holes	4.3mm Diameter, 8 Holes	
Weight	35.5g	

Performance Characteristics


Rated Speed	4700RPM ±15% @ Rated Voltage		
Air Flow	26.4CFM		
Static Pressure	0.18 Inch-H ₂ O		
Acoustic Noise	34.2dB (A)		
Insulation Class	UL Class A		
Insulation Resistance	10MΩ @ 500VDC between internal stator & lead Wire (+)		
Dielectric Strength	Applied AC 500V for one minute or AC 600V for 2 Seconds between housing & Lead Wire (+)		
Life Expectancy	60,000 Hours @ 40°C, 65% Humidity, 90% CL.		
Protection	Automatic Restart Note: In a situation where the fan is locked by an external force while The electricity is on, an increase in coil temperature will be prevented by temporarily turning off the electrical power to the motor. The fan will automatically restart when the locked rotor condition is release. Polarity Protection		



DC Axial Fan 60mm x 60mm x 15mm




Performance Curves



Dimensions

Screw Type Toward		Screw Specification	
(Pan head)	Torque	Size	Standard
Machine screw	3 to 4 Kgf-cm	M4.0	JIS B1111-1974
Self-tapping screw	5 to 6 Kgf-cm	Ø5.0	JIS B1122 Type 2

Drawing





Note: The glues on the impeller is for impeller balance. Do not remove it.

Dimensions: Millimetres

Part Number Table

	Description	Part Number
ĺ	DC Axial Fan, 60mm, Vapo, 24V, 26.4CFM, 34.2dB	MC002701

Important Notice: This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell Limited 2016.

www.element14.com www.farnell.com www.newark.com

