

HEATERS CSL 035 SCREWING FASTENING 250 W,
AC 120 V, UL



Figure similar

Model		
product brand name		SIVACON
Product designation		semiconductor fan heater
General technical data		
Active power consumption / Rated value	W	250
Operating temperature / minimum	°C	-45
Protection class		
Protection class IP		IP20
Connections		
Tightening torque / with screw-type terminals / maximum	N·m	0.8
Mechanical Design		
Depth	mm	0
Material / of the enclosure		plastic
Environmental conditions		
Ambient temperature		
• during storage / minimum	°C	-45
• during storage / maximum	°C	70
Certificates		
Equipment marking		
• acc. to DIN EN 61346-2		R
• acc. to DIN EN 81346-2		E



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8MR21505AB>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/8MR21505AB/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=8MR21505AB

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>



8MR2150-5B_ALL

last modified:

11.03.2015