


xsens



MTi 10-series

The reliable industry standard for
MEMS based IMU, VRU and AHRS



MTi 10-series

- Industry-proven, cost-effective MEMS based orientation sensor
- Full-featured sensor fusion algorithm with easy to use SDK
- 3 integration levels available: IMU, VRU and AHRS

Product Overview

	MTi-10 IMU	MTi-20 VRU	MTi-30 AHRS
Calibrated Sensor Data	yes	yes	yes
Roll/pitch (Static)	-	0.2°	0.2°
Roll/pitch (Dynamic)	-	0.5°	0.5°
Yaw	-	Active Heading Stabilization (AHS)	1.0°

Proven Xsens sensor fusion algorithm

- Superior heading tracking using Active Heading Stabilization (AHS)
- In-run Compass Calibration (ICC)
- XKF3 sensor fusion algorithm trusted by high-profile customers
- Selectable filter profiles for range of applications

Easy software integration

- Extensive suite of configurable output formats, calculated onboard the MTi
- MT Software Suite with intuitive GUI
- Complete SDK for all operating systems
- Support for Robotic Operating System (ROS)
- Xsens Xbus protocol or ASCII (NMEA)
- Access to BASE (by Xsens), an extensive knowledge base and community forum

Excellent hardware design

- High quality industrial grade components
- Signal processing pipeline, optimized for industrial applications
- Low latency for real-time applications
- 10 kHz simultaneous sampling, 2 kHz SDI algorithm with coning/sculling compensation
- Wide array of synchronization options

Specification highlights

- Available as IP67 encased MTi or OEM board
- Choice of several interfaces and onboard USB
- All Xsens products are fully interchangeable
- Cost-effective system integrator solution

Sensor specifications

	Gyroscopes	Accelerometers
Standard full range *	+/- 450 °/s	+/- 20 g
Initial bias error	0.2 °/s	5 mg
In-run bias stability	18 °/h	15 µg
Bandwidth (-3 dB)	415 Hz	375 Hz
Noise density	0.03 °/s/√Hz	60 µg/√Hz
g-sensitivity (calibrated)	0.006 °/s/g	N/A
Non-orthogonality	0.05 deg	0.05 deg
Non-linearity	0.03%	0.1%

	Magnetometer	
Standard full range	+/- 8 G	
Total RMS noise	0.5 mG	
Non-linearity	0.2%	
Resolution	0.25 mG	

* Optional +/- 1000 °/s available on request.

System specifications

Input voltage	4.5 to 34V or 3V3	Interfaces	RS232/RS422/RS485/USB/UART
Typical power consumption	550 mW @ 5V	Latency	<2 ms
IP-rating	IP67 (encased)	Sync options	SynIn, SyncOut, Clock sync
Temperature (in use)	-40 to 85 °C	Interface protocol	Xbus or ASCII (NMEA)
Casing material	Anodized aluminum 6082	Mounting orientation	No restriction, full 360° in all axes
Sampling frequency	10 kHz/channel (60 kS/s)	Built-in self test (BIT)	Gyroscopes, accelerometers, magnetometer
Clock drift	10 ppm or external reference	MTBF	300,000 hours
Output frequency	Up to 2 kHz		



MTi 10-series
Development Kit:
MTi, software and cabling



MTi encased:
57x42x23.5 mm, 52g,
9-pins push-pull connector



MTi OEM:
37x33x12 mm, 11g,
16-pins header

ABOUT XSSENS

Xsens is the leading innovator in 3D motion tracking technology and products. Its sensor fusion technologies enable a seamless interaction between the physical and the digital world in applications such as industrial control and stabilization, health, sports and 3D character animation. Clients and partners include Electronic Arts, NBC Universal, Daimler, Autodesk, ABB, Siemens and various other leading institutes and companies throughout the world. Xsens is part of mCube, the provider of the world's smallest MEMS motion sensors, key enablers for the Internet of Moving Things. Xsens has offices in Enschede, Los Angeles, Shanghai and Hong Kong.

Visit xsens.com/distributors for an overview of Xsens' worldwide distributor network



Xsens Netherlands

Xsens Technologies B.V.
P.O. Box 559
7500 AN Enschede
The Netherlands

Phone: +31 88 97367 00
Fax: +31 88 97367 01
Email: info@xsens.com

Xsens North America Inc.

101 N. Pacific Coast Hwy,
Suite 306
El Segundo, CA 90245
North America

Phone: 310-481-1800
Fax: 310-416-9044
Email: info@xsens.com

Xsens AsiaPac

Unit 208, Bldg 16W
Hong Kong Science Park
Shatin
Hong Kong

Phone: +852 3618 9080
Fax: +852 3705 8994
Email: info@xsens.com

Building 1, 2nd Floor
No.333 Huangqing Road
PRC 201899
Shanghai

Phone: +86 021 31760067
Fax: +86 021 31760067
Email: china@xsens.com

© 2005-2018, Xsens Technologies B.V. All rights reserved. Information in this document is subject to change without notice. Xsens, MTI and MTI-G are registered trademarks or trademarks of Xsens Technologies B.V. and/or its parent, subsidiaries and/or affiliates in The Netherlands, the USA and/or other countries. All other trademarks are the property of their respective owners

Unless stated otherwise, all specifications are typical. Specifications subject to change without notice.
© Xsens, August 2018



xsens

www.xsens.com