

Ecliptek is one of the ILSI America brands, which also include:



Home Products Quote Request Sample Request My Parts List Site Map Contact Us

## E1S Series Crystal

Quartz Crystal Resonator HC49/UP Short 2 Pad Surface Mount (SMD) 3.2mm Height Metal Resistance Weld Seal




Revision H 11/09/2015

### Electrical Specifications

<b>Nominal Frequency</b>	3.579545MHz to 50.000MHz <i>Some frequencies within this range may not be available.</i>
<b>Frequency Tolerance (at 25°C)</b>	±50ppm Maximum ±30ppm Maximum ±15ppm Maximum ±10ppm Maximum
<b>Frequency Stability (over Operating Temperature Range)</b>	±100ppm Maximum ±50ppm Maximum ±30ppm Maximum ±20ppm Maximum ±15ppm Maximum
<b>Operating Temperature Range</b>	0°C to +70°C -20°C to +70°C -40°C to +85°C -40°C to +105°C -40°C to +125°C -55°C to +125°C
<b>Aging at 25°C</b>	±5ppm/year Maximum
<b>Load Capacitance</b>	10pF to 50pF Parallel Resonant Series Resonant
<b>Shunt Capacitance</b>	7pF Maximum
<b>Equivalent Series Resistance</b>	<a href="#">Click to Open ESR Table</a>
<b>Mode of Operation</b>	<a href="#">Fundamental or Third Overtone</a>
<b>Crystal Cut</b>	<a href="#">AT or BT</a>
<b>Drive Level</b>	1mWatt Maximum
<b>Storage Temperature Range</b>	-55°C to +125°C
<b>Insulation Resistance</b>	Measured at 100V <sub>DC</sub> 500 Megaohms Minimum

## Mechanical Dimensions



All Dimensions in Millimeters

## Marking Specifications

Line 1:

**EXXXXXM**


- E = Ecliptek Designator
- XXXXXX = Nominal Frequency (5 Digits + Decimal)
- M = Frequency Unit of Measure (MHz)

## Environmental and Mechanical Specifications

---

<b>ESD Susceptibility</b>	MIL-STD-883, Method 3015, Class 1, HBM: 1500V
<b>Fine Leak Test</b>	MIL-STD-883, Method 1014, Condition A
<b>Flammability</b>	UL94-V0
<b>Gross Leak Test</b>	MIL-STD-883, Method 1014, Condition C
<b>Mechanical Shock</b>	MIL-STD-202, Method 213, Condition C
<b>Moisture Resistance</b>	MIL-STD-883, Method 1004
<b>Moisture Sensitivity</b>	J-STD-020, MSL1
<b>Resistance to Soldering Heat</b>	MIL-STD-202, Method 210, Condition K
<b>Resistance to Solvents</b>	MIL-STD-202, Method 215
<b>Solderability</b>	MIL-STD-883, Method 2003
<b>Temperature Cycling</b>	MIL-STD-883, Method 1010, Condition B
<b>Vibration</b>	MIL-STD-883, Method 2007, Condition A

### Tape & Reel Dimensions



1000 pieces per reel  
 Compliant to EIA-481  
 All Dimensions in Millimeters

## Fundamental Mode AT Cut

<i>Nominal Frequency Range in MHz</i>	<i>Maximum ESR in Ohms</i>
3.579545 to 4.999999	200
5.000000 to 5.999999	150
6.000000 to 7.999999	120
8.000000 to 8.999999	90
9.000000 to 9.999999	80
10.000000 to 14.999999	70
15.000000 to 15.999999	60
16.000000 to 23.999999	50
24.000000 to 30.000000	40

## Fundamental Mode BT Cut


<i>Nominal Frequency Range in MHz</i>	<i>Maximum ESR in Ohms</i>
24.000000 to 40.000000	40

## Third Overtone Mode AT Cut

<i>Nominal Frequency Range in MHz</i>	<i>Maximum ESR in Ohms</i>
24.576000 to 29.999999	150
30.000000 to 50.000000	100


## Recommended Solder Pad Dimensions

---



Tolerances =  $\pm 0.1$   
All Dimensions in Millimeters

## Solder Reflow Profile



### High Temperature Infrared/Convection

**Note:** Temperatures shown are applied to body of device.

<b><math>T_s \text{ MAX}</math> to <math>T_L</math> (Ramp-up Rate)</b>	3°C/second Maximum
<b>Preheat</b>	
- Temperature Minimum ( $T_s \text{ MIN}$ )	150°C
- Temperature Typical ( $T_s \text{ TYP}$ )	175°C
- Temperature Maximum ( $T_s \text{ MAX}$ )	200°C
- Time ( $t_s$ )	60 - 180 Seconds
<b>Ramp-up Rate (<math>T_L</math> to <math>T_p</math>)</b>	3°C/second Maximum
<b>Time Maintained Above:</b>	
- Temperature ( $T_L$ )	217°C
- Time ( $t_L$ )	60 - 150 Seconds
<b>Peak Temperature (<math>T_p</math>)</b>	260°C Maximum for 10 Seconds Maximum
<b>Target Peak Temperature (<math>T_p \text{ Target}</math>)</b>	250°C +0/-5°C
<b>Time within 5°C of actual peak (<math>t_p</math>)</b>	20 - 40 seconds
<b>Ramp-down Rate</b>	6°C/second Maximum
<b>Time 25°C to Peak Temperature (t)</b>	8 minutes Maximum
<b>Moisture Sensitivity Level</b>	Level 1

**Low Temperature Infrared/Convection**

**Note:** Temperatures shown are applied to body of device.

**T<sub>S</sub> MAX to T<sub>L</sub> (Ramp-up Rate)** 5°C/second Maximum

**Preheat**

- **Temperature Minimum (T<sub>S</sub> MIN)** N/A

- **Temperature Typical (T<sub>S</sub> TYP)** 150°C

- **Temperature Maximum (T<sub>S</sub> MAX)** N/A

- **Time (t<sub>S</sub>)** 60 - 120 Seconds

**Ramp-up Rate (T<sub>L</sub> to T<sub>P</sub>)** 5°C/second Maximum

**Time Maintained Above:**

- **Temperature (T<sub>L</sub>)** 150°C

- **Time (t<sub>L</sub>)** 200 Seconds Maximum

**Peak Temperature (T<sub>P</sub>)** 240°C Maximum

**Target Peak Temperature (T<sub>P</sub> Target)** 240°C Maximum 2 Times / 230°C Maximum 1 Time

**Time within 5°C of actual peak (t<sub>P</sub>)** 10 seconds Maximum 2 Times / 80 seconds Maximum 1 Time

**Ramp-down Rate** 5°C/second Maximum

**Time 25°C to Peak Temperature (t)** N/A

**Moisture Sensitivity Level** Level 1

**High Temperature Manual Soldering**

**Note:** Temperatures listed are applied to body of device.  
260°C Maximum for 5 seconds Maximum, 2 times Maximum.

**Low Temperature Manual Soldering**

**Note:** Temperatures listed are applied to body of device.  
185°C Maximum for 10 seconds Maximum, 2 times Maximum.



## Part Number Constructor

### Build a Part Number

Select the parameters that meet your requirements and then click the Next button below

### On the next page

Part Number specific documents, resources, and tools

#### Frequency (MHz)

*Some frequencies within this range may not be available*


#### Frequency Tolerance/Stability


#### Mode of Operation


#### Load Capacitance (pF)

(10 to 50 or leave blank for Series Resonant)

#### Packaging Options


 Part Number Specific Data Sheet


 Compliance Docs (REACH, RoHS, CMRT)

 Automated Quick Quote


 IPC-1752

 Check Stock

 My Parts List [?](#)

 Plus more

## Part Numbering Guide



#### TOOLS

- Quote Request
- Sample Request
- SmartSearch
- Compliance Documents
- Chipset Cross Reference
- Competitor Cross Reference

#### PRODUCT

- Crystals
- Oscillators
- Part Search
- REACH Resources
- RoHS Resources
- End of Life

#### ECLIPTEK

- Authorized Distributors
- Authorized Reps
- Contact
- About
- News
- Our Quality
- ISO9001
- Feedback

#### TERMS

- Privacy Policy
- Terms of Sale
- Legal