

Workshop crane, hydraulic

Mobile

Application:

For lifting heavy loads if the crane can move below the load.

Execution:

- Robust design
- Safe oil hydraulics with industry-standard engine oil
- No free overhang in front of wheels
- Mobile
- Load hook guard
- Pressure relief valve
- Drain valve with dead man's switch
- 2 steering rollers, 2 runners

Advantage:

- Robust design
- Easy to move, 360° rotating steering wheels
- Crane boom adjustable in just a few simple steps



Art. no.	77140 030
Brand	MAZZOLA/LONGUS
Manufacturer Part Number	007209036
Min./max. load-carrying capacity	500-1500 kg
Min./max. throat depth	1370-1820 mm
Min./max. construction height	1885-3300 mm
Min./max. lift height with minimum throat depth	850-2750 mm
Min./max. lift height with maximum throat depth	600-3100 mm
Inner running gear width	835 mm
Outer running gear width	1050 mm
Running gear length	1800 mm
Underride height	200 mm
Colour	Flame red RAL 3000
Load-carrying capacity	1500 kg
Max. construction height	3300 mm
Gross Weight	160.000 kg
Product Group	770