



THE PHOENIX FIRE FIGHTER sets new standards for fire and security protection and is an ideal safe for small to medium sized enterprises.

- **FIRE PROTECTION (PAPER)** – Tested to Swedish NT Fire 017-90 Paper (FS0441 & FS0442), NT Fire 017-120 Paper (FS0444), providing up to 120 minutes fire protection for paper documents.
- **FIRE PROTECTION (DIGITAL MEDIA)** – Tested to MTC DIP120-60DM fire test standard, providing 60 minutes fire protection for digital media, DVD's, USB's, memory sticks and hard drives.
- **SECURITY PROTECTION** – The safe is recommended for an overnight cash risk of £2,500 or £25,000 valuables*.
- **DROP TEST** – Fire and impact tested from 9.1 metres for resistance to the impact of falling through the burning floors of a building.
- **FITTINGS** – Each safe comes complete with height adjustable shelf and lockable cash/valuables drawer.
- **LOCKING** – **FS0440K** – Fitted with a high quality key lock supplied with two keys. **FS0440E** – Fitted with an advanced high security electronic lock with clear LED display, dual control, hidden code & scrambled code that can be programmed as standard.
- **FS0440F** – Fitted with an advanced high security touchscreen keypad & fingerprint lock with clear LED display, internal alarm, dual control, hidden code and scrambled code that can be programmed as standard with up to 128 fingerprints.
- **FIXING** – Ready prepared for floor fixing with fixing bolts for concrete supplied.
- **SPECIAL FEATURES** – Fitted with automatic slam shut door locking.
- **COLOUR** – Finished in a high quality scratch resistant white paint RAL9003.
- **GDPR** – Maintain GDPR Compliance at home or in the office by keeping your company's vital and important records secure and protected.




Internal Key Hooks

MODEL NUMBER	EXTERNAL DIMENSIONS H x W x D	INTERNAL DIMENSIONS H x W x D	DOOR SWING/ HANDLE DEPTH	UNPACKED CAPACITY WEIGHT	SHELVES / DRAWERS / INTERNAL KEY HOOKS	LEVER ARCH FOLDER	FOOLSCAP LEVER ARCH FOLDER	FOOLSCAP BOX FILE
						(H320xW75x290mm) Total no. of file per unit	(H350xW80xD285mm) Total no. of file per unit	(H370xW75xD245mm) Total no. of file per unit
FS0441K/E/F	640 x 500 x 500mm	510 ⁺ x 375 x 330mm	440mm/40mm	93kg 63 Litres	1/1/3	5	4	5
FS0442K/E/F	820 x 520 x 520mm	670 ⁺ x 380 x 330mm	460mm/40mm	120kg 84 Litres	1/1/3	10	4	5
FS0444K/E/F	1160 x 655 x 560mm	980 ⁺ x 475 x 350mm	570mm/40mm	228kg 163 Litres	2/1/5	18	10	12

This information is provided as a guide only. Actual capacities may vary depending on the storage method or shelving used.

+ The internal drawer reduces internal height by 95mm



* Ratings are approximate only and may vary due to area conditions and location. Please check with your underwriter.