Cord Connectors (Rewireable) https://www.schurter.com /PG07

## IEC Connector C21, for very hot conditions 155°C, Rewireable, Straight

16A / 250VAC; 50Hz

20A / 25<u>0VAC; 60Hz</u>

(1 min/50 Hz)

-25 °C to 155 °C

Screw clamps

> 1.5 kVAC between L-N

class I acc. to IEC 61140

> 1.5 kVAC between L/N-PE

Suitable for appliances with protection





Rewireable connector

Example with assembled cable



### Description

- Cord connector straight
- Rewireable cable assembly
- Pin temperature 155 °C , Protection class I
- Cable diameter 6.5 16 mm
- Max. wire size 1.5 mm<sup>2</sup> / 12AWG
- Min. wire size 1.0 mm<sup>2</sup>/16AWG

### **Technical Data**

Ratings UL/CSA

**Dielectric Strength** 

Allowable Operation Tempe-

Protection against electric

Ratings IEC

rature

shock Terminal See below: Approvals and Compliances

#### **Characteristics**

- Suitable for use in equipment according to IEC/UL 62368-1

## Weblinks

pdf data sheet, html datasheet, General Product Information, Approvals, Distributor-Stock-Check, Accessories, Mounting instruction, Detailed request for product

Appliance inlet/-outlet

C21 acc. to IEC 60320-1 UL 60320-1, CSA C22.2 no. 60320-1 (for very hot conditions) pin-temperature 155 °C, 16 A, Protection Class I

# Material: Housing Thermoplastic, black, UL 94V-0

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.


## Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products. Approval Reference Type: 1658

| Approval Logo | Certificates  | Certification Body | Description                              |
|---------------|---------------|--------------------|--|
| 10            | VDE Approvals | VDE                | Certificate Number: 40039959             |
| c UL us       | UL Approvals  | UL                 | UL File Number: E96454                   |
|               | CCC Approvals | CCC                | CCC Certificate Number: 2019180204010153 |

| Product standa    | rds                                |                       |   |
|-------------------|------------------------------------|-----------------------|---|
| Product standards | s that are referenced              |                       |   |
| Organization      | Design                             | Standard              | Description   |
| IEC.              | Designed according to              | IEC 60320-1           | Appliance couplers for household and similar general purposes   |
| (H)               | Designed according to              | UL 60320-1            | Standard for Attachment Plugs and Receptacles   |
| CSA<br>Group      | Designed according to              | CSA C22.2 no. 60320-1 | General Use Receptacles, Attachment Plugs, and Similar Wiring Devices   |
| Application star  |                                    |                       |   |
|                   | ards where the product can be used | 1                     |   |
| Organization      | Design                             | Standard              | Description   |
| IEC               | Designed for applications acc.     | IEC/UL 62368-1        | IEC 62368-1 includes the basic requirements for safety of audio, video, information technology and office equipment.  |
| Compliances       |                                    |                       |   |
| The product comp  | olies with following Guide Lines   |                       |   |
| Identification    | Details                            | Initiator             | Description   |
| CE                | CE declaration of conformity       | SCHURTER AG           | The CE marking declares that the product complies with the applicable<br>requirements laid down in the harmonisation of Community legislation on<br>its affixing in accordance with EU Regulation 765/2008. |
|                   | RoHS                               | SCHURTER AG           | Directive RoHS 2011/65/EU, Amendment (EU) 2015/863  |
| <u>50</u>         | China RoHS                         | SCHURTER AG           | The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.  |
| REACH             | REACH                              | SCHURTER AG           | On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration,<br>Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as<br>"REACH") entered into force.                               |

# **Dimensions** [mm]



1) Cutting points for 10/12/14/16 mm cable diameter

## **All Variants**

| Color | Max. cable diameter | Max. wire size           | Order Number |  |
|-------|---------------------|--------------------------|--------------|--|
| black | 15 mm               | 3 x 1.5 mm² / 3 x 12 AWG | 1658.0000    |  |

# Most Popular.

Availability for all products can be searched real-time:https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER

Max. torque for screws: Terminals: 0.8 Nm, Cable clamp: 0.4 Nm, Cover: 0.4 Nm

|  | Packaging unit | 50 Pcs |
|--|----------------|--------|
|--|----------------|--------|

# Mating Inlets/Plugs

Category / Description



### Appliance Inlet Overview complete

IEC Appliance Inlet C22, for very hot conditions 155°C, Screw-on or Snap-in Mounting, Front Side

1681



# IEC Inlet Filter Overview complete

C22F, Mounting: Screw Front-/Rear-Side, Filter: Standard and Medical Version, Capacitor: X2, 16 A, Solder, quick connect or wires (stranded), prewired