


# Mains Cable



## Specification

Connector A	Type J (T12)
Connector B	IEC 60320 C13
Connector Orientation	Straight
Cross-Section	0.75 mm <sup>2</sup>
Current Rating	10 A
Jacket Colour	Black
Jacket Material	PVC
Length (L)	1.8 m
Voltage Rating Max.	250 V

### Notes:

- 1.Cable:H05VV-F 3G0.75<sup>2</sup>mm Jacket  $\varnothing 6.5 \pm 0.1$  Conductor 24\*0.198
- 2.Mark:  $\triangleleft \text{VDE} \triangleright$  H05VV-F 3G0.75mm<sup>2</sup>
- 3.Test:Hi-pot: Inner Voltage AC2500V/1S , External Voltage AC4500V/1S  
current leakage 1mA, insulation resistance no less than 50M  $\Omega$ , no strike out;

**Art. Nr.**  
**RND 465-00944**