

SCXP offset solid carbide boring bar, positive, left

For face and longitudinal turning using CP indexable insert

ATORN[®]



Application

For face and longitudinal turning with CP indexable insert, 80°.

Execution

- Precision-manufactured boring bar, **solid carbide**, with internal cooling, offset, type C, attack angle 95°, tip angle 80°, clearance angle 7°

Advantage

- Universal use for face and longitudinal turning
- Positive geometry for the body ensures low cutting forces

Art. No.	17827 215
ISO name	E 12 16M SCXP R/L 05
Min. bore diameter	16 mm
Tapered diameter	12 mm
Shaft diameter	16 mm
Clearance length	55 mm
Length	150 mm
Clamping surface height	15 mm
Programming size	9 mm
Suitable for indexable inserts	CP.. 05T1..
Tool design	Right
DIN	8024

EAN-Code

4050293390322