

High-performance drill, VariDrill solid carbide TiAlN VDS40 1A 3xD with IC HA

For universal use up to 1300 N/mm²



Application:

For HPC boring up to a strength of 1300 N/mm²



Execution:

- High-performance solid carbide drill TiAlN WU25PD
- No drill heels
- Special grinding
- 30° spiral angle
- Straight main cutting edge

Advantage:

- design of VariDrill drill tip: long service life in almost all materials and fewer breakages at the cutting edge
- version without drill heel: uniform distribution of cutting forces leads to fewer breakages at the cutting edge
- design of VariDrill chip flute geometry: unhindered chip flow and problem-free chip removal

| | |
|---|-------------------|
| Art. no. | 19262 079 |
| Cutting edge diameter | 7.9 mm |
| Brand | WIDIA |
| Manufacturer Part Number | 4140376 |
| Tolerance of cutting edge diameter | m7 |
| Cutting material | SC |
| Surface | TiAlN |
| Max. drilling depth (D) | 3xD |
| Type | HPC UNI |
| Coolant supply | Internal |
| Tool holding device | HA parallel shank |
| Angle of the tip | 140 Degree |
| Shank diameter | 8 mm |
| Chip flute length | 41 mm |
| Length | 79 mm |
| f steel 1000 | 0.22 mm/r |
| Gross Weight | 0.045 kg |
| Product Group | 1XE |

EAN

4021169584237