

## BLINDNIETE



SENKKOPF 120° (~ DIN EN ISO 15980)

## BLIND RIVETS

COUNTERSUNK HEAD 120° (~ DIN EN ISO 15980)

## RIVETS AVEUGLES

AVEUGLES TÊTE FRAISÉE 120° (~ DIN EN ISO 15980)



Stahl verzinkt  
Steel zinc plated  
Acier zingué

Stahl verzinkt  
Steel zinc plated  
Acier zingué

### Ø 4,8 mm

D1 = 4,8 + 0,08 / - 0,15 mm

D2 = 9,0 + 0 / - 0,5 mm

k = -

d = 2,9 mm

P = ≥ 27,0 mm

L = + 1,0 / - 0,2 mm

4,9 mm

	F-Max		CODE					
4,8 x 8,0 mm	13,4 mm	1,5 - 4,0 mm	70811 48800	2300 N	2920 N		500	5000
4,8 x 10,0 mm	15,4 mm	3,5 - 6,0 mm	70811 48100				500	5000
4,8 x 12,0 mm	17,4 mm	6,0 - 8,0 mm	70811 48121				500	5000
4,8 x 14,0 mm	19,4 mm	8,0 - 10,0 mm	70811 48141				500	5000
4,8 x 16,0 mm	21,4 mm	10,0 - 11,5 mm	70811 48160				500	5000
4,8 x 18,0 mm	23,4 mm	11,5 - 13,5 mm	70811 48180				500	5000
4,8 x 20,0 mm	25,4 mm	13,5 - 15,5 mm	70811 48200				500	5000
4,8 x 22,0 mm	27,4 mm	15,5 - 17,5 mm	70811 48220				500	5000
4,8 x 25,0 mm	30,4 mm	17,5 - 20,5 mm	70811 48250				500	5000
4,8 x 30,0 mm	35,4 mm	20,0 - 25,0 mm	70811 48300				500	5000
4,8 x 35,0 mm	40,4 mm	25,0 - 30,0 mm	70811 48350				500	5000
4,8 x 40,0 mm	45,4 mm	30,0 - 35,0 mm	70811 48400				500	5000

### Ø 5,0 mm

D1 = 5,0 + 0,08 / - 0,15 mm

D2 = 9,0 + 0 / - 0,5 mm

k = -

d = 2,9 mm

P = ≥ 27,0 mm

L = + 1,0 / - 0,2 mm

5,1 mm

	F-Max		CODE					
5,0 x 8,0 mm	13,4 mm	1,5 - 4,0 mm	70811 50800	2575 N	3255 N		500	5000
5,0 x 10,0 mm	15,4 mm	4,0 - 6,0 mm	70811 50100				500	5000
5,0 x 12,0 mm	17,4 mm	6,0 - 8,0 mm	70811 50120				500	5000
5,0 x 14,0 mm	19,4 mm	7,0 - 9,0 mm	70811 50140				500	5000
5,0 x 16,0 mm	21,4 mm	9,0 - 11,0 mm	70811 50160				500	5000
5,0 x 18,0 mm	23,4 mm	11,5 - 13,5 mm	70811 50180				500	5000
5,0 x 20,0 mm	25,4 mm	13,0 - 15,0 mm	70811 50200				500	5000
5,0 x 25,0 mm	30,4 mm	15,0 - 20,0 mm	70811 50250				250	2500
5,0 x 30,0 mm	35,4 mm	20,0 - 25,0 mm	70811 50300				250	2500
5,0 x 35,0 mm	40,4 mm	25,0 - 30,0 mm	70811 50350				250	2500
5,0 x 40,0 mm	45,4 mm	30,0 - 35,0 mm	70811 50400				250	2500