



## BAS21/A/C/S SWITCHING DIODE


### FEATURES

- Fast Switching Speed
- Surface Mount Package Ideally Suited for Automatic Insertion
- For General Purpose Switching Applications
- High Conductance




BAS21

Marking: JS




BAS21A

Marking:JS2



BAS21C

Marking:JS3



BAS21S

Marking: JS4


### Maximum Ratings @ $T_A=25^\circ\text{C}$

Parameter	Symbol	Limits	Unit
Repetitive peak reverse voltage	$V_{RRM}$		
Working Peak reverse voltage	$V_{RWM}$	250	V
DC Blocking Voltage	$V_R$		
Forward Continuous Current	$I_{FM}$	400	mA
Average Rectified Output Current	$I_o$	200	mA
Non-Repetitive Peak Forward Surge Current @ $t = 1.0\mu\text{s}$ @ $t = 1.0\text{s}$	$I_{FSM}$	2.5 0.5	A
Repetitive Peak Forward Surge Current	$I_{FRM}$	625	mA
Power Dissipation	$P_D$	225	mW
Thermal Resistance. Junction to Ambient Air	$R_{\theta JA}$	556	°C/W
Junction temperature	$T_J$	150	°C
Storage temperature range	$T_{STG}$	-65-150	°C

### ELECTRICAL CHARACTERISTICS (Tamb=25°C unless otherwise specified)


Parameter	Symbol	Test conditions	MIN	MAX	UNIT
Reverse breakdown voltage	$V_{(BR)}$	$I_R = 100\mu\text{A}$	250		V
Reverse voltage leakage current	$I_R$	$V_R = 200\text{V}$		1	$\mu\text{A}$
Forward voltage	$V_F$	$I_F = 100\text{mA}$ $I_F = 200\text{mA}$		1000 1250	mV
Diode capacitance	$C_D$	$V_R = 0\text{V}, f = 1\text{MHz}$		5	pF
Reveres recovery time	$t_{rr}$	$I_F = I_R = 30\text{mA}, I_{rr} = 0.1 \times I_R, R_L = 100\Omega$		50	nS

## Typical Characteristics



$V_F$ , INSTANTANEOUS FORWARD VOLTAGE (V)  
Fig. 1 Forward Characteristics

## BAS21/A/C/S



$T_J$ , JUNCTION TEMPERATURE ( $^\circ\text{C}$ )  
Fig. 2 Leakage Current vs Junction Temperature