

Pneumatic two-hand grinder SBRD 8-12/2

With turning valve



Application:

For extreme brushing, grinding and milling work.

Execution:

- Rear air exhaust
- Paired bearing

Advantage:

- Optimal guidance due to extended shape and particularly stable bearing

Delivery:

Includes collet chuck ZG 7/6 mm and collet chuck key size 11 + 14; in box



Art. no.	75036 200
Brand	BIAX DRUCKLUFT
Manufacturer Part Number	150021135
Model	SBRD 820
Valve design	Rotary valve
Motor design	Vane motor
Max. idle speed	20000 rpm
Power output	300 W
Air consumption	500 l/min
Length	299 mm
Diameter of housing	38 mm
Max. clamping diameter	8 mm
Collet chuck diameter	6 mm
Max. HM rotating milling cutter diameter	12 mm
Weight	1.04 kg
Made in	Germany
Compatible with	Hose unit 001366505
Gross Weight	1.550 kg
Product Group	748