

Studs DIN 6379 for Use with Tee Nuts

Material: Tempered steel, black oxide finish. Thread rolled.


Tensile strength:

Up to M12: strength 10.9. From M14: strength 8.8.

Suitable for Tee Nuts DIN 508 or as studs for mounting a housing.

More sizes up to M36 x 700mm on request.

Ordering Details: z.B.: Product No. 655 106 032, Stud DIN 6379, M6 x 32 mm



Product No.	d mm	l mm	b ₁ mm	b ₂ mm	Weight g
655 106 032 ¹⁾	M6	32	9	16	5
655 106 050	M6	50	9	30	8
655 106 063 ¹⁾	M6	63	9	40	11
655 106 080	M6	80	9	50	13
655 108 040	M8	40	11	20	12
655 108 063	M8	63	11	40	19
655 108 100	M8	100	11	63	63
655 108 160 ¹⁾	M8	160	11	100	98
655 110 050	M10	50	13	25	24
655 110 080	M10	80	13	50	39
655 110 100 ¹⁾	M10	100	13	75	50
655 110 125	M10	125	13	75	61
655 110 160 ¹⁾	M10	160	13	100	78
655 110 200	M10	200	13	122 ²⁾	98
655 112 050	M12	50	15	25	35
655 112 063 ¹⁾	M12	63	15	32	44
655 112 080	M12	80	15	50	56
655 112 100 ¹⁾	M12	100	15	63	70
655 112 125	M12	125	15	75	88
655 112 160 ¹⁾	M12	160	15	100	112
655 112 200	M12	200	15	122 ²⁾	141
655 114 063 ¹⁾	M14	63	17	32	60
655 114 100 ¹⁾	M14	100	17	63	96
655 114 160 ¹⁾	M14	160	17	100	154
655 114 250 ¹⁾	M14	250	17	160	241
655 116 063	M16	63	19	32	80
655 116 080 ¹⁾	M16	80	19	50	103
655 116 100	M16	100	19	63	129
655 116 125 ¹⁾	M16	125	19	75	162
655 116 160	M16	160	19	100	207
655 116 200 ¹⁾	M16	200	19	122 ²⁾	260
655 116 250	M16	250	19	160	325
655 116 315 ¹⁾	M16	315	19	180	409
655 116 500 ¹⁾	M16	500	19	315	652
655 120 080	M20	80	27	32	160
655 120 125	M20	125	27	70	252
655 120 160 ¹⁾	M20	160	27	100	323
655 120 200	M20	200	27	122 ²⁾	405
655 120 250 ¹⁾	M20	250	27	160	508
655 120 315	M20	315	27	200 ²⁾	639
655 120 400 ¹⁾	M20	400	27	250	813
655 120 500 ¹⁾	M20	500	27	315	1019
655 124 100	M24	100	35	45	289
655 124 125 ¹⁾	M24	125	35	70 ²⁾	380
655 124 160	M24	160	35	100	466
655 124 200 ¹⁾	M24	200	35	122 ²⁾	585
655 124 250	M24	250	35	160	730
655 124 315 ¹⁾	M24	315	35	190	924
655 124 400	M24	400	35	250	1171
655 130 125	M30	125	43	56	573
655 130 200	M30	200	43	122 ²⁾	923
655 130 315	M30	315	43	200 ²⁾	1461
655 130 500	M30	500	43	315	2323
655 136 160	M36	160	51	80	1065
655 136 250	M36	250	51	160	1674
655 136 400	M36	400	51	250	2687

¹⁾ Not part of the DIN 6379.

²⁾ These dimensions are not part of the DIN 6379.

Mounting Example

