

## Data Sheet

---

### Coaxial Cable RG58

BN 1565756: 10 meter  
 BN 1572737: 25 meter  
 BN 1567202: 100 meter



### Technical information

Construction.....Ø0.8mm CCS + Ø3.0mm FOAM PE + AL Foil + 112x0.12mm  
 Al-Mg Alloy Wire Braiding+Ø5.0mm PVC sheath  
 Conductor..... OD:0.8 mm CCS  
 Dielectric..... OD:3.0mm Foam Polythene  
 Sheath inside..... Aluminum Foil  
 Braiding..... 112 x 0.12 Aluminum-Magnesium Alloy Wire Braiding  
 Sheath .....OD:5.0mm ROHS PVC  
 Rated Voltage.....48V DC  
 Electrical Properties.....Nominal Impedance: 75+/-5 OHM  
 .....Nom. Capacitance: 48 pF/m  
 .....Screening Factor: >52 db  
 .....Nominal Velocity of Propagation: 68 %

Max. Att	MHz	5	55	211	450	600	750	778	865	1000	1350	2279.32
(dB/100m)	dB	10.6	15.04	18.41	22.83	25.86	28.68	29.29	30.87	33.44	39.4	52.83