

## Product information

# 97 53 08 SB

## Self-Adjusting Crimping Pliers for wire ferrules

With front loading



- Compression from 0.08 - 10.0 mm<sup>2</sup> in one profile
- Wire ferrules up to 2.5 mm<sup>2</sup> can also be loaded parallel from the side
- Suitable in particular for all twin wire ferrules up to 2 x 4 mm<sup>2</sup> or 2 x AWG 12
- For crimping wire ferrules according to DIN 46228 parts 1 + 4
- Self-adjusting adaptation to the desired wire ferrule size: no wrong crimps caused by using the wrong die
- Frontal insertion of the wire ferrules into the pliers
- Repetitive, high crimping quality due to ratchet mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Handy shape and low weight provide high operation comfort
- Special quality chrome vanadium electric steel, oil-hardened

### General

Article No.	97 53 08 SB
EAN	4003773040484
Pliers	burnished
Handles	with multi-component grips
Weight	475 g
Dimensions	190 x 77 x 22 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

### Technical details




Application	Wire ferrules
Capacity in square millimetres	0.08 — 10 mm <sup>2</sup>
Number of crimping positions	1
AWG	28 — 8

*technical change and errors excepted*



97 53 08: lateral loading of wire ferrules up to 2.5 mm<sup>2</sup> parallelly from the side e.g. in confined areas



Front loading of wire ferrules e.g. in switchboards



Square-Crimp