


# 60 Watts

## VCT Series



- Low Cost
- Single Outputs from 5 V to 30 V
- Peak Load Capability
- Convection-cooled
- <0.5 W No Load Input Power
- 2"x 4" Package
- Fits 1U Applications

### Specification

#### Input

|                       |   |
|-----------------------|---|
| Input Voltage         | • 85-264 VAC                                  |
| Input Frequency       | • 47-63 Hz                                    |
| Input Current         | • 1.7 A max at 115 VAC, 0.85 A max at 230 VAC |
| Inrush Current        | • 80 A typ. at 230 VAC, cold start at 25 °C   |
| Earth Leakage Current | • 500 $\mu$ A at 264 VAC /60 Hz               |
| Power Factor          | • EN61000-3-2, class A                        |
| No Load Input Power   | • <0.5 W                                      |
| Input Protection      | • Internal T3.15A/250 V fuse in line          |

#### Output

|                          |   |
|--------------------------|---|
| Output Voltage           | • See table   |
| Output Voltage Trim      | • None  |
| Initial Set Accuracy     | • $\pm$ 2% at 50 % load   |
| Minimum Load             | • No minimum load requirement   |
| Start Up Delay           | • 2 s max   |
| Start Up Rise Time       | • 8 ms typical  |
| Hold Up Time             | • 8 ms typical at full load and 115 VAC   |
| Line Regulation          | • $\pm$ 0.5% max  |
| Load Regulation          | • $\pm$ 1.0% max (see note 1)   |
| Transient Response       | • 4% maximum deviation, recovering to less than 1% within 500 $\mu$ s for 50% step load |
| Ripple & Noise           | • 1% max pk-pk (see note 2)   |
| Overvoltage Protection   | • See table   |
| Overload Protection      | • 133-166%  |
| Short Circuit Protection | • Trip and restart (hiccup mode)  |
| Temperature Coefficient  | • 0.02% /°C   |

#### General

|                     |  |
|---------------------|--|
| Efficiency          | • See table  |
| Isolation           | • 3000 VAC Input to Output<br>1500 VAC Input to Ground<br>500 VDC Output to Ground |
| Switching Frequency | • 60 kHz $\pm$ 10 kHz  |
| MTBF                | • >700 kHrs to Bell Core iss. 6  |

#### Environmental

|                       |   |
|-----------------------|---|
| Operating Temperature | • -10 °C to +70 °C derate from 100% load at 50 °C to 50% load at 70 °C  |
| Cooling               | • Natural convection  |
| Operating Humidity    | • 5% to 90% RH, non condensing  |
| Operating Altitude    | • 3000 m  |
| Storage Temperature   | • -20 °C to +85 °C  |
| Shock                 | • IEC68-2-6, 30 g, 11 mins half sine, 3 times in each of 6 axes         |
| Vibration             | • IEC68-2-27, 10-500Hz, 2 g 10 mins / sweep. 60 mins for each of 3 axes |

#### EMC & Safety

|                      |   |
|----------------------|---|
| Emissions            | • EN55032, level B conducted & radiated                                     |
| Harmonic Currents    | • EN61000-3-2 class A   |
| Voltage Flicker      | • EN61000-3-3   |
| ESD Immunity         | • EN61000-4-2, level 3, Perf Criteria A                                     |
| Radiated Immunity    | • EN61000-4-3, 10 V/m, Perf Criteria A                                      |
| EFT/Burst            | • EN61000-4-4, level 3, Perf Criteria A                                     |
| Surge                | • EN61000-4-5, installation class 3, Perf Criteria A                        |
| Conducted Immunity   | • EN61000-4-6, 10 V, Perf Criteria A  |
| Dips & Interruptions | • EN61000-4-11, 30% 10 ms, 60%, 100 ms, 100%, 5000 ms Perf Criteria A, B, B |
| Safety Approvals     | • UL60950-1, IEC60950-1, EN60950-1, UL62368-1, EN62368-1, IEC62368-1        |


Models and Ratings

| Output Voltage <sup>(6)</sup> | Output Current |                     | OVP Setting <sup>(5)</sup> | Efficiency <sup>(4)</sup> | Model Number |
|-------------------------------|----------------|---------------------|----------------------------|---------------------------|--------------|
|                               | Nominal        | Peak <sup>(3)</sup> |                            |                           |              |
| 5.0 V                         | 8.00 A         | 10.0 A              | 7.0 V                      | 82%                       | VCT40US05    |
| 12.0 V                        | 5.00 A         | 6.3 A               | 13.0 V                     | 87%                       | VCT60US12    |
| 15.0 V                        | 4.00 A         | 5.0 A               | 17.0 V                     | 87%                       | VCT60US15    |
| 24.0 V                        | 2.50 A         | 3.1 A               | 29.0 V                     | 88%                       | VCT60US24    |

Notes

1. Load regulation is measured from 60% to full load and from 60% to 20% load (60% ±40% full load).
2. Measured at the output connector with a 0.1 μF ceramic capacitor and a 10 μF electrolytic capacitor.
3. Peak load lasting <30 s with a maximum duty cycle of 10%, average output power not to exceed nominal.
4. Average of efficiencies measured at 25%, 50%, 75% & 100% load and 230 VAC input.
5. Typical trip point.
6. Other voltages between 5 V and 30 V available on request, contact sales for details.

Mechanical Details



| Output Connector |       |
|------------------|-------|
| 1                | +Vout |
| 2                | +Vout |
| 3                | -Vout |
| 4                | -Vout |

Mates with: Molex Housing 09-50-3041 and Molex Series 2878 crimp terminals.

| Input Connector |         |
|-----------------|---------|
| Pin 1           | Neutral |
| Pin 2           | Live    |

Mates with: Molex Housing 09-50-3031 and Molex Series 2878 crimp terminals.

Mounting holes marked with ⊕ must be connected to safety earth

Notes

1. All dimensions shown in inches (mm).
2. Weight 0.29 lbs (130 g) approx
3. Tolerance: x.xx = ±0.04 (x.x = ±0.1); x.xxx = ±0.2 (x.xx = ±0.5)