



# 24828-205 INTERSCALE FAN HOLDER WITH FAN, 2 U, 310W, 221D, 1 FAN (80 X 80 X 25)





# **KEY FEATURES**

Fan holder for mounting on bottom of case

Fans are simple to fit to the fan holder using vibration-damping fixing material

Fan holders fix into desktop case with 2 plastic feet or into 19" case with 2 screws

Fan holder cannot be used in conjunction with the mounting plate (instead use mounting plate with integrated fan holder)

For technical data of fans, please see delivery includes

## **PRODUCT ATTRIBUTES**

Product Type: Fan Unit

Product Family: Interscale

Type: Fan Tray

Input Voltage DC: 12 V min

Depth: 25 mm

Height: 80 mm

Width: 80 mm

Max Ambient Temperature: 70 °C

Airflow: 19 m³/h

Noise Level: 32 dB(A)

Power: 2 W

## ADDITIONAL PRODUCT DETAILS

Interscale Fan Holder With Fans, for desktop cases and 19" chassis. Available in different sizes and with three fan versions, with a air flow volume from 10 to 170 m<sup>3</sup>/h.

#### **North America**

All locations +1.763.422.2661 Chat with us: schroff.nyent.com

## Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: schroff.nvent.com

nVent.com

## Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: schroff.nvent.com

#### Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: schroff.nvent.com



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2023 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.