

## Push rod clamp

Short form



### Application:

For quick and secure clamping on machine tables and appliances.

### Execution:

- Compression and tension clamp - short model
- Galvanised and passivated
- Fitting screws tempered
- Long push rod version
- Case-hardened and lubricated bearing bushes
- With red oil-resistant plastic handle
- Rivet made of stainless steel
- Ergonomic, oil-resistant handle with large hand rest and soft components.

### Delivery:

With tempered and galvanised thrust bolt



<b>Art. no.</b>	<b>26218 050</b>
<b>Brand</b>	AMF
<b>Manufacturer Part Number</b>	94334
<b>Size</b>	5
<b>Clamping stroke</b>	67 mm
<b>Retaining force</b>	4000 N
<b>Clamping height</b>	37 mm
<b>Length</b>	175 mm
<b>Min./max. adjustment range</b>	30-50 mm
<b>Height</b>	149 mm
<b>Thumbscrew size</b>	M12 x 50 mm
<b>Gross Weight</b>	0.931 kg
<b>Product Group</b>	260

### EAN

4020772094331