

Product characteristics

Inductive sensor

Metal thread M30 x 1.5

Connector

Sensing range 15 mm; [nf] non-flush mountable

Electrical data

Electrical design

Operating voltage [V]

Protection class

Reverse polarity protection

Outputs

Output function

Voltage drop [V]

Minimum load current [mA]

Leakage current [mA]

**Current rating**

- Current rating (continuous) [mA]

- Current rating (peak) [mA]

Short-circuit proof

Overload protection

Switching frequency [Hz]

Range

Sensing range [mm]

Real sensing range (Sr) [mm]

Operating distance [mm]

Accuracy / deviations

Correction factors

Hysteresis [% of Sr]

Switch-point drift [% of Sr]

Environment

Ambient temperature [°C]

Protection

Tests / approvals

EMC

MTTF [Years]


Mechanical data

	AC/DC
Operating voltage [V]	20...250 AC/DC
Protection class	II
Reverse polarity protection	yes
Output function	normally open
Voltage drop [V]	< 6.5
Minimum load current [mA]	5
Leakage current [mA]	< 2.5 (250 V AC) / < 1.3 (110 V AC) / < 0.8 (24 V DC)
- Current rating (continuous) [mA]	250 AC / 100 DC; 350 AC (...50 °C)
- Current rating (peak) [mA]	î: 2.2 A (20 ms / 0.5 Hz)
Short-circuit proof	no
Overload protection	yes
Switching frequency [Hz]	25 AC / 50 DC
Sensing range [mm]	15
Real sensing range (Sr) [mm]	15 ± 10 %
Operating distance [mm]	0...12.1
Correction factors	mild steel = 1 / stainless steel approx. 0.7 / brass approx. 0.5 / Al approx. 0.4 / Cu approx. 0.3
Hysteresis [% of Sr]	3...15
Switch-point drift [% of Sr]	-10...10
Ambient temperature [°C]	-25...80
Protection	IP 67
EMC	EN 60947-5-2 EN 55011: class B
MTTF [Years]	607

# II0256 - Inductive sensor - eclass: 27270101 / 27-27-01-01

Mounting	non-flush mountable
Housing materials	Brass nickel-plated; PBT (Pocan)
Weight [kg]	0.172
Displays / operating elements	
Output status indication LED	yellow
Electrical connection	
Connection	M18 connector

## Wiring



Note: miniature fuse to IEC60127-2 sheet 1,  
 $\leq 2$  A (fast acting)

Accessories	
Accessories (included)	2 lock nuts
Remarks	
Remarks	Recommendation: check the unit for reliable function after a short circuit.
Pack quantity [piece]	1