

Combination wrench (DIN 3113 A) with special coating

DIN 3113 A, jaw angle 15°, ring side angled 15°

ATORN[®]



Version

- With completely new special surface
- Maximum resistance against contact corrosion
- 15x greater corrosion protection against exposure to temperature, road salt and environmental influences compared to conventionally coated keys
- Up to 720 hours in the salt spray test in accordance with DIN EN ISO 9227
- Environmentally friendly chromium-VI-free coating process
- Made from chromium-vanadium steel, die-forged and hardened.
- DIN 3113 A

Advantage

- Extremely durable and robust industrial design

Art. No.	52034 007
Width across flats	7 mm
Length	110 mm
Tip profile type	ENERGY profile
Jaw position	15 Degree
Surface	Special coating according to specifications
Material	Chrome-vanadium steel
DIN	3113

EAN-Code

4050293536904