

Wall-mounted swivelling crane boy (BW) – with chain hoist with foot-pull fastening

With retractable boom




Application:

The folding boom makes it ideal for loading machines or confined spaces

Execution:

- Classification in accordance with EN 13001 HC2 S2 HD2 for lightweight industrial applications in production halls
- Round cable power supply in the boom profiles right up to the boom tip
- Lockable isolating switch
- Operating voltage: 400 V/50 Hz, control voltage: 24 V
- Electric chain hoist with „foot-mounted hoist suspension“ – 2-stage lifting speed – without gear limit switches – pre-assembled



Advantage:

- Folding boom
- Fast handling of workpieces
- Long hook path thanks to chain hoist with foot-mounted hoist suspension
- Swivel resistance is adjusted manually as standard

Delivery:

Includes detailed documentation, electric chain hoist with foot-mounted hoist suspension

Art. no.	77110 015
Brand	VETTER
Manufacturer Part Number	BW2,5-4,0+ST0502-0
Model	Boy BW
Type	Console assembly A
Load-carrying capacity	250 kg
Overhang	4000 mm
Overhang 1	2100 mm
Overhang 2	1900 mm
Construction height	940 mm
Lifting device design	Electric chain hoist with foot-mounted hoist attachment
Swivel range	300 Degree
Colour	Daffodil yellow RAL 1007
Surface	Lacquered
Operating voltage	400 V
Cable length	3 m
Weight	205 kg
Max. vertical force	5 kN
Max. horizontal force	21 kN
Gross Weight	223.000 kg
Product Group	7EL