

PM-D F5 F. MOTOR STARTER POWER MODULE, FAILSAFE EXPANSION TO PM-D F1 TO F4, CONTACT MULTIPLIER W. 4 FLOATING RELAY CONTACTS, DC 24V MAX. 3A PER CONTACT PLUGABLE ONTO TM-PF30 S47-D0 30MM



Figure similar

General technical data:

product brand name		Local Safety Modules
Product designation		PM-D F5
Protection class IP		IP20
Product function		
• Bus communication		Yes
• Short circuit protection		No
Operating current at 400 V Rated value	A	4
SIL Claim Limit (subsystem) acc. to EN 62061		3
Category acc. to EN ISO 13849-1		4
Electrical endurance (switching cycles) typical		200 000
Mechanical service life (switching cycles) typical		10 000 000

Control circuit/ Control:

Type of voltage of the control supply voltage		DC
Control supply voltage for DC		
• Rated value	V	24
• Rated value	V	28.8 ... 20.4

Installation/ mounting/ dimensions:

Width	mm	30
Height	mm	196.5
Depth	mm	117.5

Certificates/ approvals:

General Product Approval	Functional Safety/Safety of Machinery	Declaration of Conformity
--------------------------	---------------------------------------	---------------------------



[Type Examination Certificate](#)



Test Certificates	other
-------------------	-------

[Type Test Certificates/Test Report](#)

[Environmental Confirmations](#)

[Confirmation](#)

[Declaration of Conformity](#)

#### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RK19031BE00>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<http://support.automation.siemens.com/WW/view/en/3RK19031BE00/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

<http://www.automation.siemens.com/bilddb/index.aspx?attID9=3RK19031BE00&lang=en>

last modified:

15.01.2015