

Approvals



## Low Cost PCB Filter




- Rated currents from 0.5 to 6.5A
- Compact PCB-mountable design
- Very low profile
- Optional medical versions (B type)

### Technical specifications

Datasheet Image:	FN_402_white_01.jpg
Design corresponding to :	UL 1283, CSA 22.2 No. 8 1986, IEC/EN 60939
Flammability corresponding to:	UL 94V-0
High potential test voltage :	P → PE 2000 VAC for 2 sec (standard types) P → PE 2500 VAC for 2 sec (B types) P → N 760 VAC for 2 sec
Maximum continuous operating voltage :	250VAC, 50/60Hz
MTBF @ 40°C/230V (Mil-HB-217F) :	1,900,000 hours
Operating frequency:	dc to 400Hz
Performance indicators:	FN402.jpg
Rated currents :	0.5 to 6.5 A @ 40°C max.
Temperature range (operation and storage) :	-25 °C to +100 °C (25/100/21)

### Typical electrical schematic



The FN 402 PCB filter is a single-phase filter designed for easy and fast PCB-mounting. Choosing the FN 402 product line brings you the rapid availability of a standard filter associated with the necessary safety acceptance. Standard PCB single-phase filters are a practical solution helping you to pass EMI system approval in a short time. A selection on amperage ratings and medical types are designed to offer you the desired standard product.

### Features and benefits

- Good conducted attenuation performance, based on chokes with high saturation resistance and excellent thermal behavior.
- PCB through hole mounting.
- Low cost low profile.
- Custom specific versions on request.

### Typical applications

- Electrical and electronic equipment
- Small to medium-sized machines and household equipment
- Single-phase power supplies, switch-mode power supplies
- Test and measurement equipment
- Medical equipment


**Filter selection table**

Filter	Rated current @ 40°C (25°C)	Leakage current* @ 230VAC/50Hz	Inductance L	Capacitance		Resistance R	Input/Output connections	Weight [g]
	[A]	[mA]	[mH]	Cx [μF]	Cy [nF]	[kΩ]		
FN402-0.5-02	0.5 (0.6)	373	40	100	2.2	1000	-02	40
FN402-1-02	1 (1.2)	373	10	100	2.2	1000	-02	40
FN402-1.6-02	1.6 (1.9)	373	6	100	2.2	1000	-02	40
FN402-2.5-02	2.5 (3)	373	2	100	2.2	1000	-02	40
FN402-4-02	4 (4.7)	373	1	100	2.2	1000	-02	40
FN402-6.5-02	6.5 (7.5)	373	1	100	2.2	1000	-02	40
FN402B-0.5-02	0.5 (0.6)	2	40	100		1000	-02	40
FN402B-1-02	1 (1.2)	2	10	100		1000	-02	40
FN402B-1.6-02	1.6 (1.9)	2	6	100		1000	-02	40
FN402B-2.5-02	2.5 (3)	2	2	100		1000	-02	40
FN402B-4-02	4 (4.7)	2	1	100		1000	-02	40
FN402B-6.5-02	6.5 (7.5)	2	1	100		1000	-02	40

\* Maximum leakage under normal operating conditions. Note: if the neutral line is interrupted, worst case leakage could reach twice this level.

**Product selector**

FN 402x-yy-..



02: PCB through hole mounting

0.5 to 6.5: Rated current

Blank: Standard version

B: Medical version (without Y2-capacitor)



For example: FN 402-0.5-02, FN 402B-6.5-02

**Typical filter attenuation**

Per CISPR 17; A = 50Ω/50Ω sym; B = 50Ω/50Ω asym; C = 0.1Ω/100Ω sym; D = 100Ω/0.1Ω sym


0.5 to 1.6A types

2.5 to 6.5A types




**Mechanical data**

FN 402



FN 402B



All dimensions in mm; 1 inch = 25.4mm

Tolerances according: ISO 2768-m / EN 22768-m

**Headquarters, global innovation  
and development center**

**Schaffner Group**

Nordstrasse 11  
4542 Luterbach  
Schweiz  
T +41 32 681 66 26  
F +41 32 681 66 30  
[info\(at\)schaffner.com](mailto:info(at)schaffner.com)  
[www.schaffner.com](http://www.schaffner.com)

To find your local partner within  
Schaffner's global network, please go  
to [www.schaffner.com](http://www.schaffner.com)

© 2012 Schaffner Group  
Specifications are subject to change  
within notice. The latest version of the  
data sheets can be obtained from the  
website. All trademarks recognized.

Schaffner is an ISO-registered  
company.

Its products are designed and  
manufactured under the strict quality  
and environmental requirements of  
the ISO 9001 and ISO 14001  
standards.

This document has been carefully  
checked. However, Schaffner does not  
assume any liability for errors or  
inaccuracies.

**Sales and application centers**

**China**

**Schaffner EMC Ltd. Shanghai**  
T20-3, No 565 Chuangye Road  
Pudong New Area  
Shanghai 201201  
T +86 21 3813 9500  
F +86 21 3813 9501 / 02  
[cschina@schaffner.com](mailto:cschina@schaffner.com)  
<http://www.schaffner.com.cn/>

**Finland**

**Schaffner Oy**  
Sauvonrinne 19 H  
Lohja 08500  
T +358 19 35 72 71  
[finlandsales@schaffner.com](mailto:finlandsales@schaffner.com)

**France**

**Schaffner EMC S.A.S.**  
112, Quai de Bezons, Boîte postale 133  
Argenteuil 95103  
T +33 1 34 34 30 60  
F +33 1 39 47 02 28  
[francesales@schaffner.com](mailto:francesales@schaffner.com)

**Germany**

**Schaffner Deutschland GmbH**  
Westring 18  
Büren 33142  
T +49 2951 60 01 0  
F +49 2951 60 01 23  
[buerensales@schaffner.com](mailto:buerensales@schaffner.com)

**Italy**

**Schaffner EMC S.r.l.**  
Via Galileo Galilei 47  
Cinisello Balsamo (MI) 20092  
T +39 02 66 04 30 45/47  
F +39 02 61 23 943  
[italysales@schaffner.com](mailto:italysales@schaffner.com)

**Japan**

**Schaffner EMC K.K.**  
1-32-12, Kamiyama, Setagaya-ku  
Mitsui-Seimei Sangenjaya Bldg. 7F  
Tokyo 154-0011  
T +81 3 5712 3650  
F +81 3 5712 3651  
[japansales@schaffner.com](mailto:japansales@schaffner.com)  
<http://www.schaffner.jp>

**Singapore**

**Schaffner EMC Pte Ltd.**  
Blk 3015A Ubi Road 1 05-09 Kampong Ubi  
Industrial Estate  
Singapore 408705  
T +65 6377 3283  
F +65 6377 3281  
[singaporesales@schaffner.com](mailto:singaporesales@schaffner.com)

**Spain**

**Schaffner EMC España**  
Miniparc III, Edificio E  
Madrid 28109  
T +34 618 176 133  
[spainsales@schaffner.com](mailto:spainsales@schaffner.com)

**Sweden**

**Schaffner EMC AB**  
Turebergstorg 1, 6  
Sollentuna 19147  
T +46 8 5792 1121 / 22  
F +46 8 92 96 90  
[swedensales@schaffner.com](mailto:swedensales@schaffner.com)

**Switzerland**

**Schaffner EMV AG**  
Nordstrasse 11  
Luterbach 4542  
T +41 32 6816 626  
F +41 32 6816 641  
[sales@schaffner.ch](mailto:sales@schaffner.ch)

**Taiwan R.O.C.**

**Schaffner EMV Ltd.**  
6F. No. 413 Rui Guang Road  
Neihu District Taipei City 114  
T +886 2 87525050  
F +886 2 87518086  
[taiwansales@schaffner.com](mailto:taiwansales@schaffner.com)

**Thailand**

**Schaffner EMC Co. Ltd.**  
Amphur Muang P.O. Box 14  
Northern Region Industrial Estate 67 Moo 4  
Tambon Ban Klang  
Lamphun 51000  
T +66 53 58 11 04  
F +66 53 58 10 19  
[thailandsales@schaffner.com](mailto:thailandsales@schaffner.com)

**UK**

**Schaffner Ltd.**  
Molly Millars Lane Wokingham  
Berkshire RG41 2PL  
T +44 118 9770070  
F +44 118 9792969  
[uksales@schaffner.com](mailto:uksales@schaffner.com)  
<http://www.schaffner.uk.com>

**USA**

**Schaffner EMC Inc.**  
52 Mayfield Avenue  
Edison 08837  
T 1-800-367-5566  
T 732-225-9533  
F 732-225-4789  
[usasales@schaffner.com](mailto:usasales@schaffner.com)  
<http://www.schaffner.com/us>