

Thread go ring gauge

For standard metric ISO thread // improved corrosion resistance

ATORN®

Application


For testing the flank and core diameter of male threads.

Version

- Surface hardness approx. 2500 Vickers

Advantage

- Improved corrosion resistance
- Wear resistance approx. 10 times greater than conventional gauge steel
- Extended calibration intervals
- Cost reduction



Art. No.	32697 200
Calibration Group	AB
Thread type	Metric thread
Thread type x nominal diameter x pitch	M20 x 2.5
Pitch	2.5 mm
Tolerance class	6g
Material	TiN
DIN	2285-1

EAN-Code

4050293202632